

## Snap Rivets / Removable

72.21.361

Product No. 72.21.361

<b>Model</b>	Snap Rivets
<b>Design</b>	Flat Head, raund Head-Desing
<b>Mounting Hole Dia.</b>	3.1-3.2 mm
<b>Panel Thickness</b>	5.5-6.5 mm
<b>Body length</b>	8.00 mm
<b>Material</b>	Nylon-6 UL94 V-2 / E41871
<b>Special Features</b>	Shaft: Fig. 1, Slot
<b>Color</b>	Black
<b>Head Diameter</b>	6.40 mm
<b>Finish</b>	1.6mm
<b>Prong Diameter</b>	3.00 mm
<b>RoHS II compliant</b>	yes
<b>Reach/SVHC free</b>	yes

**Similar products** Snap Rivet ø3.0/5.0-6.5mm panel  
Polyamid 6,white  
72.21.369

