

Round Spacer / Wall Thickness 1,8 8,4/12x12 Steel zinc plated

05.68.121

Product No. 05.68.121

Model	Metal Spacers
Type	Standard, cut ends
Design	Cut
Inner Diameter	for M8- Dia.8.0-8.8
Outer Diameter	12.00 mm
Length	12.00 mm
Material	Steel
Plating	Zinc, Clear Chromate
Special Features	004T Material
RoHS II compliant	yes
Reach/SVHC free	yes

Similar products Round Spacer / Wall Thickness 1,8
8,4/12x12 Brass nickel plated
05.68.123

