



Ultra Bright Slimline LED Table Lamp

D35127

This powerful LED table lamp will add value to any home, office or beauty salon with its super high-quality slim brushed chrome design and powerful 2,100 Lux bright light at 30cm.

This lamp uses only 9W of energy but provides an incandescent bulb equivalent of 200W of light.

Supplied with touch sensitive dimmer switch, with 3 different settings.

It provides 90cm/35" long arm reach and even wide coverage of light which is ideal for large work surfaces. The daylight™ technology also reduces eye strain and glare for healthy vision and allows true colour correcting for colour matching when painting or looking at photographs.



100% flexible,
100% practical



5,400 lux



daylight™
technology



Eco-friendly



Metal table
clamp included



Slim &
lightweight



Ultra Bright Slimline LED Table Lamp

D35127

Overview

- Irresistible high-quality brushed chrome metal finish, Slimline design
- 3 Full-spectrum ultra-bright daylight™ LED strips
- Bright 200W of light, using only 9W of energy
- Lamp brightness 2,100 Lux at 30cm
- Total amount of visible light emitted in Lumens is 614 lm
- Double flexible arm with 90cm/35" reach for wide spread of light
- Slimline design - light and material in perfect balance
- Dimmer switch with 3 settings
- Height adjustable from 15 to 55cm / 6 to 21"
- Comfortable and safe low heat light
- Great colour matching, see the true colours
- Supplied with high quality metal clamp
- Slimline table base available separately (D/A52107)



Technical information

Packaging information

Item code	D35127
Colour box width	530mm (20.87 in)
Colour box depth	60mm (2.36 in)
Colour box height	195mm (7.68 in)
Total packed weight	1.55kg (3½ lbs)
Products per carton	4

Product information

Assembled Width	85cm (33½ in)
Assembled Height	35cm (14 in)
Assembled Depth	2cm (1 in)
Assembled Weight	1.03kg (2½ lbs)
Length of cable	2.0m
Main colour	Silver

Light output information

Light source type	LED
Total wattage	9w

Contact us

The Daylight Company Ltd
Info.uk@daylightcompany.com
UK + 44 (0)20 8964 1200
FR 0825 00 49 46
DE 0800 329 2667

