


PRODUCT SPECIFICATION

Brand	C.K
Product Range	Files and rasps
Catalogue number	0069, 0071, 0072, 0073, 0074, 0075, 0079, 0080, 0082, 0083, 0106, 0107, 0119, 0120 & 0124
Date	20/02/2009

Range Description
A range of professional quality files and rasps

- Features**
- All**
- All file blades are made from high carbon steel, hardened and tempered for strength and durability
 - Two component file handles feature a softer outer with solid core and shock absorbing inner plug – for safety, performance and comfort






0083



0106



0107



0119



0120 1



0120 2



0120 3




0120 4



0120 5



0120 6



Item Number	Item Description	EAN No	Commodity code	Carton Qty
T0069 1	File Handle 2 Component 6"	-	39269097	12
T0069 2	File Handle 2 Component 8"	-	39269097	1
T0069 3	File Handle 2 Component 10/12"	-	39269097	1
T0071	File Handle Wood	5013969388206	44219098	6
T0072 5	Saw File Extra Slim 5"	5013969388305	82031000	6
T0073 6	Saw File Slim 6"	5013969388404	82031000	3
T0074 6	Saw File Standard 6"	5013969388503	82031000	3
T0075 10	Mill Saw File 10"	5013969388701	82031000	3
T0079 1	Chain Saw File 6 x 5/32"	5013969389807	82031000	3
T0079 2	Chain Saw File 8 x 3/16"	5013969389906	82031000	6
T0079 3	Chain Saw File 8 x 7/32"	5013969390001	82031000	6
T0080 10	Engineers File Flat 10" 2nd Cut	5013969816303	82031000	3
T0080 6	Engineers File Flat 6" 2 nd Cut	5013969390100	82031000	3
T0080 8	Engineers File Flat 8" 2 nd Cut	5013969390209	82031000	3
T0080B 10	Engineers File Flat 10" Bastard	5013969337006	82031000	3
T0080S 6	Engineers File Flat 6" Smooth	5013969390308	82031000	3
T0080S 8	Engineers File Flat 8" Smooth	5013969390407	82031000	3
T0082 10	Engineers File H/Round 10" 2nd Cut	5013969816600	82031000	3
T0082 6	Engineers File H/Round 6" 2nd Cut	5013969390506	82031000	3
T0082 8	Engineers File H/Round 8" 2nd Cut	5013969390605	82031000	3

T0083 10	Engineers File Round 10" 2nd Cut	5013969816907	82031000	3
T0083 6	Engineers File Round 6" 2nd Cut	5013969390704	82031000	3
T0083 8	Engineers File Round 8" 2nd Cut	5013969390803	82031000	3
T0106 06	Hand File/Rasp 6"	5013969391503	82031000	3
T0106 08	Hand File/Rasp 8"	5013969391602	82031000	3
T0107 06	Wood Rasp 6"	5013969391701	82031000	3
T0107 08	Wood Rasp 8"	5013969391800	82031000	3
T0119	Warding File Set/4	5013969391909	82031000	3
T0120 1	Warding File Hand	5013969700831	82031000	6
T0120 2	Warding File Flat	5013969700848	82031000	6
T0120 3	Warding File Half Round	5013969700855	82031000	6
T0120 4	Warding File Round	5013969700862	82031000	6
T0120 5	Warding File Square	5013969700879	82031000	6
T0120 6	Warding File 3 Square	5013969700886	82031000	6
T0120P	Warding File Set/6	5013969392609	82031000	3
T0124P	Needle File Set/6	5013969395501	82031000	3

Technical product information	
Standards compliance	None applicable
User health and safety information	None applicable
RoHS/WEEE compliance	This product range does not fall within the scope of RoHS or WEEE regulations
Material safety data	None applicable
Warranty	C.K Tools are guaranteed for life against imperfect materials or workmanship Normal wear and tear or damage caused through inappropriate use is not covered
Country of origin	Italy - 0069, 0071, 0079 Germany – 0072, 0073, 0074, 0075, 0080, 0082, 0083, 0106, 0107, 0119, 0120, 0124P

Dimensional details

Item	Product only				Product on primary packaging			
	Width mm	Depth mm	Height mm	Net weight g	Width mm	Depth mm	Height mm	Gross weight g
T0069 1	23	15	96	22	-	-	-	-
T0069 2	28	18	110	38	-	-	-	-
T0069 3	30	22	125	56	-	-	-	-

T0071	11	11	90	18	60	13	170	24
T0072 5	23	15	225	44	25	15	250	48
T0073 6	25	6	245	66	25	15	250	68
T0074 6	25	15	245	108	25	15	260	112
T0075 10	28	25	365	252	41	25	265	262
T0079 1	23	15	220	36	25	15	260	40
T0079 2	25	15	295	50	35	15	320	56
T0079 3	25	15	295	58	35	15	320	62
T0080 10	27	20	365	302	40	20	325	312
T0080 6	25	15	245	94	25	15	260	98
T0080 8	25	15	300	168	35	15	320	174
T0080B 10	27	20	360	286	40	20	370	296
T0080S 6	25	15	245	102	25	15	260	106
T0080S 8	25	15	300	180	25	15	310	186
T0082 10	27	25	365	264	40	25	380	274
T0082 6	23	15	245	94	25	15	260	100
T0082 8	27	20	320	176	35	20	320	182
T0083 10	30	20	360	176	40	20	370	188
T0083 6	25	15	240	50	27	15	260	54
T0083 8	30	20	300	112	35	15	320	118
T0106 06	23	15	250	72	25	15	250	76
T0106 08	27	20	310	208	35	20	315	214
T0107 06	25	15	250	94	25	15	260	100
T0107 08	27	20	310	166	25	20	320	172
T0119	70	15	230	74	70	15	230	74
T0120 1	13	13	160	18	-	-	-	-
T0120 2	13	13	160	20	-	-	-	-
T0120 3	13	13	160	28	-	-	-	-
T0120 4	13	13	160	12	-	-	-	-
T0120 5	13	13	160	18	-	-	-	-
T0120 6	13	13	160	14	-	-	-	-
T0120P	-	-	-	-	100	14	230	126
T0124P	-	-	-	-	65	5	200	48

Item	Shelf box (secondary packaging)				Euro Pallet data Wi x Hi	
	Width mm	Depth mm	Height mm	Gross weight g	No of cartons on base	Number of rows high
T0069 1	90	160	65	312		
T0069 2	-	-	-	-		
T0069 3	-	-	-	-		
T0071	145	220	31	196		
T0072 5	90	25	290	292		
T0073 6	90	25	290	218		
T0074 6	90	25	290	344		
T0075 10	65	400	52	846		
T0079 1	90	25	290	126		
T0079 2	140	30	330	356		
T0079 3	65	400	52	454		
T0080 10	65	400	52	1005		
T0080 6	90	25	290	328		
T0080 8	65	400	52	615		
T0080B 10	65	400	52	965		
T0080S 6	90	25	290	312		
T0080S 8	150	15	340	565		
T0082 10	65	400	52	890		
T0082 6	100	15	290	294		
T0082 8	65	400	52	605		
T0083 10	65	400	52	625		
T0083 6	100	18	290	176		
T0083 8	65	400	52	420		
T0106 06	100	18	290	278		
T0106 08	65	400	52	685		
T0107 06	100	18	290	304		
T0107 08	65	400	52	585		
T0119	80	45	260	234		
T0120 1	80	14	180	118		
T0120 2	80	14	180	126		
T0120 3	80	14	180	174		
T0120 4	80	14	180	76		
T0120 5	80	14	180	114		

T0120 6	80	14	180	90		
T0120P	150	45	320	384		
T0124P	150	15	220	144		

Packaging waste details

Item	Primary Packaging				Secondary packaging			
	Plastic g	Use	Card g	Use	Plastic g	Use	Card g	Use
T0069 1							48	Box
T0069 2								
T0069 3								
T0071	6	Wallet					52	Box
T0072 5	4	Wallet			4	Bag		
T0073 6	4	Wallet			6	Bag		
T0074 6	4	Wallet			6	Bag		
T0075 10	10	Wallet					58	Box
T0079 1	4	Wallet			6	Bag		
T0079 2	6	Wallet			12	Bag		
T0079 3	4	Wallet					58	Box
T0080 10	10	Wallet					58	Box
T0080 6	4	Wallet			6	Bag		
T0080 8	6	Wallet					58	Box
T0080B 10	6	Wallet					58	Box
T0080S 6	4	Wallet			6	Bag		
T0080S 8	6	Wallet			12	Bag		
T0082 10	10	Wallet					58	Box
T0082 6	4	Wallet			6	Bag		
T0082 8	6	Wallet					58	Box
T0083 10	12	Wallet					58	Box
T0083 6	4	Wallet			6	Bag		
T0083 8	6	Wallet					58	Box
T0106 06	4	Wallet			6	Bag		
T0106 08	6	Wallet					58	Box
T0107 06	6	Wallet			6	Bag		
T0107 08	6	Wallet					58	Box
T0119	10	Wallet			6	Bag		

T0120 1					6	Bag		
T0120 2					6	Bag		
T0120 3					6	Bag		
T0120 4					6	Bag		
T0120 5					6	Bag		
T0120 6					6	Bag		
T0120P					6	Bag		
T0124P					6	Bag		