

Full-Motion Desk Mount for 13" to 27" Flat-Screen Displays

MODEL NUMBER: **DDR1327S**



Highlights

- **REPLACES MODEL DDR1323S**
- Increases available desk/table space in office workstation applications
- Fits most flat-panel displays from 13" to 27"
- Convenient one-touch display adjustment for easy view optimization and improved ergonomics
- Full range of motion with -40° to +90° tilt, 180° swivel and 360° rotation capability
- Supports up to 20 lb
- 5-year warranty

Package Includes

- DDR1327S Full-Motion Flat-Screen Desk Mount
- Mounting Hardware
- Owner's Manual

Description

Tripp Lite's sleekly designed, VESA-compliant DDR1327S Full-Motion Flat-Screen Desk Mount frees up valuable space in your workstation and allows you to re-position your display for increased viewing comfort and improved ergonomics. It features convenient one-touch display adjustment with tilt, swivel and rotation capabilities and fits most 13- to 27-inch flat-panel displays. Its durable, all-metal frame with soft, rubber feel finish withstands the stress of repeated use and blends easily into any décor. It comes with all necessary mounting hardware and supports weights of up to 20 lb. For peace of mind, the DDR1327S comes backed by a 5-year warranty.

Features

- Tripp Lite's sleekly designed, VESA-compliant DDR1327S Full-Motion Flat-Screen Desk Mount frees up valuable space in your workstation and allows you to re-position your display for increased viewing comfort and improved ergonomics
- Convenient one-touch display adjustment with tilt, swivel and rotation capabilities and fits most 13- to 27-inch flat-panel displays
- Durable, all-metal frame with soft, rubber feel finish withstands the stress of repeated use and blends easily into any décor
- Includes all necessary mounting hardware and supports weights of up to 20 lbs
- 5-year warranty

Specifications

PHYSICAL	
Mounting Location	Desktop
Unit Weight (lbs.)	11.55
Unit Weight (kg)	5.23
Color	Black
Screen Size Compatibility (in.)	13 - 27



Tripp Lite
1111 W. 35th Street
Chicago, IL 60609 USA
Telephone: 773.869.1234
www.tripplite.com

Screen Size Compatibility (cm)	33.02 - 68.50
VESA Pattern (mm)	75x75; 100x100
Motion	Full
Degrees of Motion	-40/+90 Tilt; 180 swivel; 360 rotate
Min/Max Arm Extension (in.)	19.68
Min/Max Arm Extension (cm)	50
Maximum Weight Capacity (lbs.)	20
Maximum Weight Capacity (kg)	9
FEATURES & SPECIFICATIONS	
Tools Necessary	Yes
Cord Management	Yes
WARRANTY	
Product Warranty Period (U.S. & Canada)	5-year limited warranty

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>