

## 4x4 HDMI over Cat5/Cat6 Matrix Splitter Switch, Transmitter for Video and Audio, 1920x1200 1080p at 60Hz

MODEL NUMBER: **B126-4X4**



### Description

Tripp Lite's B126-4X4 HDMI over Cat5/6 Matrix Splitter Switch and Transmitter Unit allows you to share high-definition video and audio from four HDMI-enabled digital video components (e.g., DVR, Cable Box, Blu-Ray, HD gaming consoles, etc.) to four different monitors. When used with Tripp Lite Active HDMI receivers, it can extend a 1080P signal up to 125ft, and 1080i up to 175ft. By daisy chaining three units together, you can connect up to 4 monitors per video channel. The B126-4X4 is HDCP- and EDID-compatible and provides you with a variety of installation options. Plug-and-play convenience makes for an easy, efficient setup and switching between inputs is simple via pushbuttons, remote, or RS232 serial control options. Included with the product is a 5-ft. IR extension cable that allows you to extend the range in which the remote control can be used. It also allows for the B126-4X4 to be discreetly placed out of view, while maintaining remote control functionality.

### Features

- Share multiple HDMI sources between multiple monitors
- Allows any input to be routed to any output; or the same input to be routed to multiple outputs
- Transmits the signal over one Cat5e/6 cable to a remote monitor up to 175 ft. away
- A B126-Series remote receiver is needed at each monitor
- For longer distances: Use a B126-1A0 or B126-1A0-WP-1 active remote receiver to extend a 1080p @ 60Hz signal up to 125 ft. from the transmitter (or a 1080i @ 60Hz signal up to 175 ft. from the transmitter)
- For shorter distances: Use a B126-1P0 or B126-1P0-WP-1 passive remote receiver to extend a 1080p @ 60Hz signal up to 50 ft. from the transmitter (or a 1080i @ 60Hz signal up to 75 ft. from the transmitter)
- Use 24AWG, Solid Wire Cat5e/6 cable, such as Tripp Lite's N202-Series, to achieve maximum distance and resolution
- Further expand the range and number of monitors by adding B126-110 remote repeater units
- Add up to three repeaters on each channel of the matrix switch, for a total of 4 displays per channel (An active remote receiver should be the last unit in a channel)
- A 1080p @ 60Hz signal can be extended up to 125 ft. for each repeater added into a channel (or up to 175 ft. for a 1080i @60Hz signal)

### Highlights

- Routes HDMI sources over Cat5e/6 cable to four different monitors up to 175 ft. away
- Add up to three repeaters on each channel of the matrix switch, for a total of 4 displays per channel
- Switch input sources via Push-button, Remote, or RS232 serial
- HDCP-compatible
- Plug-and-play; no software or drivers required
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

### Package Includes

- B126-4X4 Transmitter Unit
- External Power Supply (Input: 100-240V, 50/60Hz, 0.5A Output B126-2X2: 5V, 2A
- 3.5 mm to DB9 Adapter Cable ( serial )
- Mounting Hardware
- Remote Control
- IR Extension Cable
- Owner's Manual



- Switch between inputs via pushbuttons, remote control, or RS232 serial
- Included 5-ft. IR extension cable allows you to extend the range in which the remote control can be used, and/or to locate the B126-4X4 discreetly out of view, while maintaining remote control functionality.
- HDCP-compatible
- Mounting hardware included
- Plug-and-play; no software or drivers required
- Compatible with all operating systems
- Compliant with the Federal Trade Agreements Act (TAA) for GSA Schedule purchases

## Specifications

OVERVIEW	
Display Style	Extender
Cable Type	UTP (Cat5, Cat5e, Cat6, Cat6a); VGA
PHYSICAL	
Unit Dimensions (hwd / in.)	1.20 x 5.9 x 3.90
Unit Dimensions (hwd / cm)	3.05 x 14.99 x 9.91
Included Mounting Accessories	Yes
Color	Black
ENVIRONMENTAL	
Operating Temperature Range	0 to 40 C (32 to 104 F)
Storage Temperature Range	-20 to 60 C (-4 to 140 F)
Relative Humidity	20 to 90%
CONNECTIONS	
Connector A	HDMI (FEMALE) (X4)
Connector B	RJ45 (FEMALE) (X4)
Ports	8
SPECIAL FEATURES	
Chromebook Compatible	Yes
WARRANTY	



**Tripp Lite**  
1111 W. 35th Street  
Chicago, IL 60609 USA  
Telephone: 773.869.1234  
[www.tripplite.com](http://www.tripplite.com)

Product Warranty Period (Worldwide)	1-year limited warranty
-------------------------------------	-------------------------

© 2015 Tripp Lite. All rights reserved. All product and company names are trademarks or registered trademarks of their respective holders. Use of them does not imply any affiliation with or endorsement by them. Tripp Lite has a policy of continuous improvement. Specifications are subject to change without notice.

Tripp Lite uses primary and third-party agencies to test its products for compliance with standards. See a list of Tripp Lite's testing agencies:

<http://www.tripplite.com/products/product-certification-agencies>