



Ega Communication trunking is a series of unobtrusive low profile PVCu trunkings designed to contain the smaller diameter cables used for telecommunication and signal purposes. There are three sizes available and the systems are complete with fittings to enable them to be used in conjunction with the mini trunking boxes.

All extrusions manufactured from 90% recycled material.*

* Based on 2008 consumption.

Communication Trunking

3 METRE LENGTHS

2 METRE LENGTHS (NON UK)



11 x 8mm	CMT1WHI	60m	CMT1D1WHI	60m
16 x 10mm	CMT3WHI	60m		
20 x 12.5mm	CMT4WHI	60m		

STANDARD LENGTH: 3 metres

2 metre lengths are available for Non UK Markets.

MATERIAL: PVCu
COLOUR: White

Available in 2 metre lengths for non UK markets.

Speedfix™ Trunking

3 METRE LENGTHS

2 METRE LENGTHS (NON UK)

Self adhesive tape should not be relied upon for permanent fixing of the Speedfix range. Additional fixing means (such as screws) should be used.



Spout Adaptor



Circular Box

ONE ENTRY

Circular Box Through

TWO ENTRY



11 x 8mm	SMT1WHI	60m	SMT1D1WHI	60m	CMA1WHI	25		
16 x 10mm	SMT3WHI	60m	SMT3D1WHI	60m	CMA3WHI	25		
20 x 12.5mm	SMT4WHI	60m	SMT4D1WHI	60m	CMA4WHI	25	YCR1001ELWHI 10	YCR1002ELWHI 10

Available in 2 metre lengths for non UK markets.

Spout adaptors are for use with switch and socket boxes.

Circular boxes accept standard ceiling roses and pull switches. The base incorporates earth terminal facility (order terminal separately, see page 370).

LID FIXING CENTRES: 50.8mm

PILLAR THREAD SIZE: M4 (Metal inserts)

LOAD SUSPENSION: 5kg @ 60°C max