#### ST 18/3-pole plug components

## 250 V, 16 A

# ST 18/3

### Terminal connection: single

Strain relief device: for PVC-sheathed flexible cord 1x round cable Ø 6.5–8.3 mm

Sheath strip length: 28 mm Insulation strip length: 7 mm

28 53



Plug component unassembled with strain relief device without locking device 93.932.3353.0 1 200

**93.932.3353.0** 1 200 **93.932.3350.0** 200 93.932.3750.0 200

Plug component unassembled with strain relief device with locking device

**93.932.4353.0** 200 **93.932.4350.0** 200 93.932.4750.0 200

Part no. Box O



Plug component 93.032.3353.0 200 93.032.3350.0 200 93.032.3750.0 200

# Terminal connection: single

Strain relief device: for PVC-sheathed flexible cord 1x round cable Ø 6.5–8.3 mm 2x round cable Ø 5.5–7.2 mm 1x flat cable 4.6 x 8.1 mm

Sheath strip length: 28 mm Insulation strip length: 7 mm

28 53



Plug component unassembled with strain relief device without locking device

**93.832.3353.0** 200 **93.832.3350.0** 200 93.832.3750.0 200

Plug component unassembled with strain relief device with locking device 93.832.4353.0 200

**93.832.4353.0** 200 **93.832.4350.0** 200 93.832.4750.0 200

Part no. Box Oty




Plug component 93.032.3353.0 200 93.032.3350.0 200 93.032.3750.0 200

#### Terminal connection: dual

Strain relief device: for PVC-sheathed flexible cord 1 x round cable Ø 6.5–8.3 mm

Sheath strip length: 28 mm Insulation strip length: 7 mm





Plug component unassembled with strain relief device without locking device 93.932.6353.0 200

93.932.6350.0 200

Plug component unassembled with strain relief device with locking device 93.932.7353.0 200 93.932.7350.0 200

Part no. Box Qt



Plug component 93.032.6353.0 200 93.032.6350.0 200

#### Terminal connection: dual

Strain relief device: for PVC-sheathed flexible cord 1x round cable Ø 6.5–8.3 mm 2x round cable Ø 5.5–7.2 mm 1x flat cable 4.6 x 8.1 mm

Sheath strip length: 28 mm Insulation strip length: 7 mm

5555 78



Plug component unassembled with strain relief device without locking device 93.832.6353.0 200 93.832.6350.0 200

Plug component unassembled with strain relief device with locking device 93.832.7353.0 200

93.832.7350.0 200

Part no. Box Qt



Plug component 93.032.6353.0 200 93.032.6350.0 200



Strain relief device without locking device, base and top **Z7.410.8153.0** 200

**Z7.410.8153.0** 200 **Z7.410.8150.0** 200

Strain relief device with locking device, base and top Z7.410.8353.0 200 Z7.410.8350.0 200

Plug component green, strain relief device black

(Note: observe coding!)



Strain relief device without locking

device, base and top **Z7.410.5153.0** 200 **Z7.410.5150.0** 200

Strain relief device with locking device, base and top

**Z7.410.5353.0** 200 **Z7.410.5350.0** 200

Plug component green, strain relief device black (Note: observe coding!)



Strain relief device without locking

**Z7.410.8253.0** 200 **Z7.410.8250.0** 200

Strain relief device with locking

device, base and top Z7.410.3453.0 200 Z7.410.3450.0 200



Strain relief device without locking device, base and top

**Z7.410.5253.0** 200 **Z7.410.5250.0** 200

Strain relief device with locking device, base and top

**Z7.410.3353.0** 200 Z7.410.3350.0 200