# S-11 SINGLE CONTACT BAYONET BASE


## MINIATURE LAMP

**28V 0.900A**

| WAMCO PART NO. | ENVELOPE SIZE | BASE TYPE | RATING | FILAMENT SHAPE |
|---|---|---|---|---|
| WL-309 | S-11 | BA15s | 28V 0.900A | C-2V |

| | CURRENT (A) | | | LIGHT OUTPUT (MSCP) | | | |
|---|---|---|---|---|---|---|---|
| TEST VOLTS | MIN | NOM | MAX | MIN | NOM | MAX | LIFE HRS |
| 28V | .810 | .900 | .990 | 25.6 | 32.0 | 38.4 | 300 |

## DIMENSIONAL CHARACTERISTICS




## NOTES

1. LCL = 1.25" (31.8mm)
2. Nickel-plated brass construction base
3. Part mark WL-309
4. RoHS compliant
5. ANSI trade number 309

P: (714) 545-5560 F: (714) 545-6093
W: WWW.WAMCOINC.COM E: INFO@WAMCOINC.COM