

HP DeskJet 2130 All-in-One Printer



The easy way to print, scan and copy

Make your everyday printing, scanning and copying easy with an HP DeskJet all-in-one that simply works – right out of the box. Save money with optional high-yield ink cartridges. Plus, save space with an all-in-one designed to fit where you need it.



Highlights

- **Print Speed:** Up to 7.5 ppm ISO black (A4); Up to 5.5 ppm ISO colour (A4)
- **Easy setup**
- **Affordable basic AIO for the home**

Get just what you need – right away

- Count on easy versatility. Print, scan and copy what you need quickly with a reliable all-in-one.

It's easy from the start

- Get started in fewer steps. Easily set up this all-in-one to print, scan and copy with simple controls.
- Save your space with a compact all-in-one designed to fit on your desk, on a shelf or anywhere you need it.

Tackle more tasks affordably

- Print more for less, using the world's No. 1 printer brand plus Original HP ink cartridges.¹
- Full of value – print up to twice as many pages with Original HP high-yield ink cartridges.²

Reduce your impact

- Conserve resources without sacrificing performance with an all-in-one that's ENERGY STAR® certified.
- Reduce your environmental impact – count on easy, free cartridge recycling through HP Planet Partners.³



Easy Set up



HP DeskJet 2130 All-in-One Printer

Technical specifications

Functions	Print, copy, scan
Print speed	Up to 7.5 ppm ISO black (A4); Up to 5.5 ppm ISO colour (A4)
Print resolution	Up to 1200 x 1200 rendered dpi black; Up to 4800 x 1200 optimised dpi colour (when printing from a computer on selected HP photo papers and 1200 input dpi)
Print technology	HP Thermal Inkjet
Print Area	Print margins: Top: 3 mm; Bottom: 14.5 mm; Left: 3 mm; Right: 3 mm; Maximum print area: 216 x 355 mm
Print languages	HP PCL 3 GUI
Print capabilities	Borderless printing: No
Print cartridges number	2 (1 each black, tri-colour)
Mobile printing capability	No
Monthly duty cycle	Up to 1,000 pages (A4); Recommended monthly page volume: 50 to 100
Automatic paper sensor	No
Multitasking supported	No
Wireless Capability	No
Connectivity	Standard 1 Hi-Speed USB 2.0
Network Capabilities	No
Memory	Standard Integrated; Maximum Integrated
Printer smart software features	Manual Duplex
Copier settings	Auto-enlarge; Maximum number of copies: Up to 9 copies; Copy resolution: Up to 600 x 300 dpi; Copy resolution, color text and graphics: Up to 600 x 300 dpi; Up to 5 cpm black ISO (A4), Up to 3 cpm colour ISO (A4)
Copy speed	Up to 5 cpm black ISO (A4), Up to 3 cpm colour ISO (A4)
Scanner specifications	Scanner type: Flatbed; Scan technology: Contact Image Sensor (CIS); Scan input modes: Front-panel scan; Twain version: Version 1.9; Scan size maximum (flatbed, ADF): 216 x 297 mm; Optical scan resolution: Up to 1200 dpi
Scan file format	JPEG, TIFF, PDF, BMP, PNG
Scannable area	Maximum media size: 216 x 297 mm
Bit depth/ Greyscale levels	24-bit/ 256
Digital sending	Standard: No
Fax	No
Media types	Plain paper, photo paper, brochure paper
Media sizes	Supported A4; B5; A6; DL envelope; Custom: 89 x 127 to 215 x 279 mm
Media Handling	Input capacity: Up to 60 sheets; Up to 20 cards cards; Up to 20 sheets photo paper Output capacity: Up to 25 sheets, Up to 5 envelopes Maximum: Up to 25 sheets Duplex printing: Manual (driver support provided)
Paper weight	Supported: A4: 60 to 90 g/m ² ; HP envelopes: 75 to 90 g/m ² ; HP cards: up to 200 g/m ² ; HP 10 x 15 cm photo paper: up to 300 g/m ² ; Recommended: 75 g/m ²

What's in the box	F5540B: HP DeskJet 2130 All-in-One Printer; HP 302 Black Ink Cartridge (~190 pages); HP 302 Tri-color Ink Cartridge (~165 pages); Software CD; Setup poster; Power cord; [For ink volume and page yield information, visit http://www.hp.com/go/learnaboutsupplies]
Supplies	F6U65AE HP 302 Tri-color Original Ink Cartridge ~165 pages F6U66AE HP 302 Black Original Ink Cartridge ~190 pages F6U67AE HP 302XL High Yield Tri-color Original Ink Cartridge ~330 pages F6U68AE HP 302XL High Yield Black Original Ink Cartridge ~480 pages
Compatible operating systems	Windows 10, Windows 8.1, Windows 8, Windows 7; Mac OS X v10.8 Mountain Lion, OS X v10.9 Mavericks, OS X v10.10 Yosemite
Minimum system requirements	Windows: Windows 10, 8.1, 8, 7: 1 GHz 32-bit (x86) or 64-bit (x64) processor, 2 GB available hard disk space, CD-ROM/DVD drive or Internet connection, USB port, Microsoft® Internet Explorer; Windows Vista: 800 MHz 32-bit (x86) or 64-bit (x64) processor, 2 GB available hard disk space, CD-ROM/DVD drive or Internet connection, USB port, Internet Explorer 8 Mac: OS X v10.8 Mountain Lion, OS X v10.9 Mavericks, OS X v10.10 Yosemite; 1 GB available hard disk space; Internet; USB
Printer dimensions (W x D x H)	Minimum: 425 x 304 x 149 mm; Maximum: 424.97 x 519.36 x 248.77 mm (with input and output tray/extension extended)
Package dimensions (W x D x H)	475 x 191 x 354 mm
Printer Weight	3.42 kg
Package weight	4.48 kg
Operating environment	Temperature: 5 to 40°C, Humidity: 20 to 80% RH
Storage	Temperature: -40 to 60°C, Humidity: 5 to 90% RH (non-condensing)
Acoustics	Acoustic power emissions: 6.2 B(A); Acoustic pressure emissions: 48 dB(A)
Power	Requirements: Input voltage: 100 to 240 VAC (+/- 10%), 50/60 Hz (+/- 3 Hz) Consumption: 10 watts (maximum), 10 watts (active), 0.1 watts (off), 1.9 watts (standby), 0.9 watts (sleep) Power supply type: Built-in power supply
Certifications	CISPR 22:2008/EN 55022:2010 Class B; CISPR 24:2010/EN 55024:2010; EN 61000-3-2:2006 +A1:2009 +A2:2009; EN 61000-3-3:2008; EAC (Russia) Energy Star Qualified: Yes
Country of origin	Made in China
Warranty	One-year limited hardware warranty, 24-hour, 7 days a week Web support
Service and support	UG062E HP 3 year Care Pack w/Next Day Exchange for Multifunction Printers UG187E HP 3 year Care Pack w/Standard Exchange for Multifunction Printers (UG062E: only Austria, Belgium, Denmark, Finland, France, Germany, Ireland, Italy, Netherlands, Norway, Portugal, Spain, Sweden, Switzerland, UK, Czech Republic, Greece, Hungary, Poland, Slovakia, UG187E: all EMEA countries)

Footnotes

¹Based on IDC's Worldwide Quarterly Hardcopy Peripherals Tracker®, 2012 Q4. Shipments for inkjet single-function printers and multifunction printers, including production units.; ²Based on HP 63XL High Yield Black Original Ink Cartridges. High-yield ink cartridges not included; purchase separately. For more information, see <http://www.hp.com/go/learnaboutsupplies>. Less cost per page compared with estimated street price and published page yield of standard-yield HP 63 Original Ink Cartridges. Actual pricing may vary.; ³Programme availability varies. Original HP cartridge return and recycling is currently available in more than 50 countries, territories and regions in Asia, Europe and North and South America through the HP Planet Partners programme. For more information, visit <http://www.hp.com/recycle>.



<http://www.hp.com/uk>

The product could differ from the images shown. © Copyright 2015 HP Development Company, L.P. The information contained herein is subject to change without notice. The only warranties for HP products and services are set forth in the express warranty statements accompanying such products and services. Nothing herein should be construed as constituting an additional warranty. HP shall not be liable for technical or editorial errors or omissions contained herein.

4AA5-9182EEE, November 2015

