

**PICCOLO ABS M 95 T**



Sample photo

**Order symbol:** ABS M 95 T  
**Product nbr:** 8784018  
**Description:** Enclosure, ABS  
**Remarks:** Transparent cover

**EAN:** 6418074002327  
**EI. number:**  
 Finland: 3423569  
 Electric No. 8212002089  
 Denmark:  
 Electric No. Italy: 7212060  
 Electric No. Sweden: 2536759

Including: Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

| Dimensions: | Length | Width | Height | Accessories: |                            |
|-------------|--------|-------|--------|--------------|----------------------------|
| mm:         | 230    | 140   | 95     | CHM-3        | DIN-35 Mounting rail       |
| inch:       | 9.1    | 5.5   | 3.7    | FM-3         | DIN-35 Mounting rail       |
|             |        |       |        | FP 22046     | Wall fastening lug (4 pcs) |

| Materials:                    |                      | Rating:                                  |
|-------------------------------|----------------------|--|
| <b>Material:</b>              | ABS                  | Ingress Protection (EN 60529): IP66/IP67 |
| <b>Base colour:</b>           | RAL 7035 -light grey | Impact Resistance (EN 62262): IK07       |
| <b>Cover screws material:</b> | Polyamide            | Electrical insulation: Totally insulated |
| <b>Cover colour:</b>          | Clear transparent    | Halogen free (DIN/VDE 0472, Part 815): 1 |
| <b>Cover screws colour:</b>   | Grey                 | Flammability Rating: UL 94 HB            |
| <b>Gasket material:</b>       | Polyurethane         | Glow Wire Test (IEC 695-2-1) °C: 650     |
|                               |                      | NEMA Class: NEMA 1, 4, 4X, 6, 6P, 12, 13 |

| Temperatures:                       |                |
|-------------------------------------|----------------|
| <b>Temperature °C (short term):</b> | -40 ... 80 °C  |
| <b>Temperature °C (continuous):</b> | -40 ... 60 °C  |
| <b>Temperature °F (short term):</b> | -40 ... 175 °F |
| <b>Temperature °F (continuous):</b> | -40 ... 140 °F |

| Accessories: |                |
|--------------|----------------|
| M-MP         | Mounting plate |

