

MNX PC 100/50 LT



Sample photo

Order symbol: PC 100/50 LT
Product nbr: 6012902
Description: Enclosure, PC
Remarks: Smoked transparent cover

EAN: 6418074052391
El. number:
Finland: 3420418
Electric No. Denmark: 8212022593
Electric No. Sweden: 6012902

Including: Base with TPE gasket, screws for mounting plate/DIN-rail and cover with polyamide cover screws.

Dimensions:			Accessories:		
mm:	130	80	50	MIN 5	DIN-15 Mounting rail
inch:	5.1	3.1	2.0	MIN 10	DIN-15 Mounting rail
			MIV 5	DIN-35 Mounting rail	
			MIV 10	DIN-35 Mounting rail	
Materials:			FP A 100/130	Front plate (Aluminium)	
Material:	Polycarbonate		HFP 130	Front plate hinge series	
Base colour:	RAL 7035 -light grey		FP 22046	Wall fastening lug (4 pcs)	
Cover screws material:	Polyamide				
Cover colour:	Smoked grey				
Cover screws colour:	Black				
Gasket material:	TPE				
Temperatures:			Rating:		
Temperature °C (short term):	-40 ... 120 °C		Ingress Protection (EN 60529): IP66/IP67		
Temperature °C (continuous):	-40 ... 80 °C		Impact Resistance (EN 62262): IK08		
Temperature °F (short term):	-40 ... 250 °F		Electrical insulation: Totally insulated		
Temperature °F (continuous):	-40 ... 175 °F		Halogen free (DIN/VDE 0472, Part 815): 1		
Accessories:			UV resistance: UL 508		
MIV 100	Mounting plate (Galvanized steel)		Flammability Rating: UL 746C 5V		
			Glow Wire Test (IEC 695-2-1) °C: 960		
			NEMA Class: NEMA 1, 4, 4X, 6		
			Certificates:		
			Germanischer Lloyd (GL)		
			SGS Fimko		
			Gost R		

