

EK EKHA 130 G



Sample photo

Order symbol:	EKHA 130 G
Product nbr:	2538001
Description:	Enclosure, PC
Remarks:	Grey cover

EAN: 6418074013446
El. number:
 Finland: 3425400
 Electric No. Italy: 7501010
 Electric No. Sweden: 2538001

Including: Flanged Base with screws for mounting plate/DIN-rail, cover with PUR gasket and polyamide cover screws.

Dimensions:	Length	Width	Height
mm:	190	190	130
inch:	7.5	7.5	5.1

Materials:

Material:	Polycarbonate
Base colour:	RAL 7035 -light grey
Cover screws material:	Polyamide
Cover colour:	RAL 7035 -light grey
Cover screws colour:	Grey
Gasket material:	Polyurethane

Temperatures:

Temperature °C (short term):	-40 ... 120 °C
Temperature °C (continuous):	-40 ... 80 °C
Temperature °F (short term):	-40 ... 250 °F
Temperature °F (continuous):	-40 ... 175 °F

Accessories:

EKHA Base. PC

Accessories:

EKHS	Base, PC
EKH 30-G	Cover
EKH 80-G	Cover
EKH 30-T	Cover
EKH 80-T	Cover
EKHVT	Mounting plate
EKHXT	Mounting plate Pertinax
EKV 12	DIN-35 Mounting rail

Rating:

Ingress Protection (EN 60529): IP66/IP67
Impact Resistance (EN 62262): IK08
Electrical insulation: Totally insulated
Halogen free (DIN/VDE 0472, Part 815): 1
UV resistance: UL 508
Flammability Rating: UL 746C 5V
Glow Wire Test (IEC 695-2-1) °C: 960
NEMA Class: NEMA 1, 3, 3S, 4, 4X, 6, 6P, 12

Certificates:

- Germanischer Lloyd (GL)
- SGS Fimko
- Lloyds Register of Shipping (LR)
- Gost R

EK 190x190x130-180

