

PT-P700

Professional PC Labelling Machine



Top Features:

Easy connectivity

- No software or printer driver installation Needed. Simply connect, design then print

Compact, elegant and easy to use

- Compact design uses little desk space

Professional software

- Built in P-touch Editor Lite and Ptouch Editor 5.1 that works on Windows® and Macintosh®

3 power options

- AC adaptor, AA alkaline battery or NiMH battery

High speed printing

- Print at up to 30mm/sec

Advanced cutter

- Built-in cutter with auto cut feature

General

Carton contents	PT-P700 labelling machine 24mm black on white 4m tape cassette CD Quick set-up guide AC adaptor
------------------------	---

Language support	English, German, French, Spanish, Portuguese, Italian, Dutch, Danish, Norwegian, Swedish, Finnish, Hungarian, Czech, Polish, Romanian, Slovenian, Slovakian, Croatian, Turkish, Brazilian Portuguese
-------------------------	--

Dimensions & Weights

Without carton	78(w) x 152(d) x 143(h) † 710g
-----------------------	--------------------------------

Built In Features

Printing speed	30mm/second (using AD adaptor)
-----------------------	--------------------------------

Print resolution	180 x 360dpi
-------------------------	--------------

Interfaces	USB
-------------------	-----

Maximum print height	18.1mm
-----------------------------	--------

Cutter type	Automatic full cutter
--------------------	-----------------------

Label length	30mm minimum † 300mm maximum
---------------------	------------------------------

Operating system support	Microsoft Windows® Vista, Windows® 7, Windows® 8, Mac OS/X 10.6.8 to 10.8.x
---------------------------------	---

Software (P-touch Editor Lite)

(P-touch Editor 5.1)

Language support	English, French, German, Dutch, Italian, Spanish, Portuguese, Danish, Norwegian, Swedish, Finnish, Czech, Hungarian, Polish	English, French, German, Dutch, Italian, Spanish, Portuguese, Danish, Norwegian, Swedish
-------------------------	---	--

Number of fonts	All installed true type fonts	All installed true type fonts
------------------------	-------------------------------	-------------------------------

Image support	BMP, JPG, TIFF, PNG, GIF, DIB, WMF, WMF, EMF, ICO, JPEG, Screen capture function	BMP, JPG, TIFF, PNG, GIF, DIB, WMF, WMF, EMF, ICO, JPEG, Screen capture function
----------------------	--	--

Number of templates	N/A	88
----------------------------	-----	----

Number of frames	10	154
-------------------------	----	-----

Label length setting	25-300mm	25-1000mm
-----------------------------	----------	-----------

Number of barcodes	None	21
---------------------------	------	----

Sequential numbering	1-200, A-Z, a-z	1-5000, A-Z, a-z
-----------------------------	-----------------	------------------

Number of copies	1-200	1-5000
-------------------------	-------	--------

Database support	None	csv, txt, mdb, xls, AccdbMicrosoft® SQL server database (Windows® only)
-------------------------	------	---

Load/Save label design	Yes	Yes
-------------------------------	-----	-----

Tape size and colour detection	Yes	Yes
---------------------------------------	-----	-----

Supplies

Tape type	TZe
------------------	-----

Tape widths	3.5, 6, 9, 12, 18 and 24mm
--------------------	----------------------------

Optional Accessories

Batteries	AA alkaline/rechargeable batteries (LR6/HR6)
------------------	--

AC adaptor	AD-E001
-------------------	---------