

PT-P750W

Professional PC Labelling Machine with Wireless LAN & NFC



Top Features:

Easy connectivity

- No software or printer driver installation needed . Simply connect, design then print

Work wirelessly

- Print from Windows, Macintosh and iOS, Android devices using the iPrint&Label App (for general office use)

Professional software

- Built in P-touch Editor Lite and Ptouch Editor 5.1 that works on Windows® and Macintosh®

4 power options

- AC adaptor, AA alkaline battery, AA NiMH battery or Li-ion rechargeable battery

Hi speed printing

- Print at up to 30mm/sec

Advanced cutter

- Built-in cutter with half cut feature produces easy-to-peel labels

Compact, elegant and easy to use

- Compact design uses little desk space



Brother
iPrint&Label App

General

Carton contents	PT-P750W labelling machine 24mm black on white 4m tape cassette AC Adaptor USB cable User's Guide
Language support	English, German, French, Spanish, Portuguese, Italian, Dutch, Danish, Norwegian, Swedish, Finnish, Hungarian, Czech, Polish, Romanian, Slovenian, Slovakian, Croatian, Turkish, Brazilian Portuguese

Dimensions & Weights

Without carton	78(w) x 152(d) x 143(h) 800g
-----------------------	--------------------------------

Built In Features

Printing speed	30mm/second (using AD adaptor)
Print resolution	180 x 360 dpi
Interfaces	USB, Wireless (802.11b/g/n), NFC
Maximum print height	18.1mm
Cutter type	Automatic full and half cutter
Label length	30mm minimum 300mm maximum
Operating system support	Microsoft Windows® Vista, Windows® 7, Windows® 8, Mac OS/X 10.7 to 10.9.

Software (P-touch Editor Lite)

(P-touch Editor 5.1)

Language support	English, French, German, Dutch, Italian, Spanish, Portuguese, Danish, Norwegian, Swedish, Finnish, Czech, Hungarian, Polish	English, French, German, Dutch, Italian, Spanish, Portuguese, Danish, Norwegian, Swedish
Number of fonts	All installed true type fonts	All installed true type fonts
Image support	BMP, JPG, TIFF, PNG, GIF, DIB, WMF, WMF, EMF, ICO, JPEG, Screen capture function	BMP, JPG, TIFF, PNG, GIF, DIB, WMF, WMF, EMF, ICO, JPEG, Screen capture function
Number of templates	N/A	88
Number of frames	10	154
Label length setting	25-300mm	25-1000mm
Number of barcodes	None	21
Sequential numbering	1-200, A-Z, a-z	1-5000, A-Z, a-z
Number of copies	1-200	1-5000
Database support	None	csv, txt, mdb, xls, Accdb, Microsoft® SQL server database (Windows® only)
Load/Save label design	Yes	Yes
Tape size and colour detection	Yes	Yes

Supplies

Tape type	TZe
Tape widths	3.5, 6, 9, 12, 18 and 24mm
Batteries	BA-E001 Li-ion rechargeable battery AA alkaline/rechargeable batteries (LR6/HR6)
AC adaptor	AD-E001

Optional Accessories

iPrint&Label

Mobile operating system support	iOS 5.0 or higher, Android 2.2 or higher
Language support	English, French, German, Dutch, Italian, Spanish, Portuguese, Danish, Norwegian, Swedish, Czech, Hungarian, Polish, Finnish, Polish, Croatian, Romanian, Slovakian, Russian
Image support	Photo function
Template	Yes (*Number TBD)
Label collection	Yes (*Number TBD)
Tape size and colour detection	Yes
Label length setting	24-600mm
Quote address book	Yes
Portrait Print	Yes