

REL50L0C2



Article Number: 115-00600

Releasable Cable Tie, 9.8" Long, 50 lb Tensile Strength, PA66, Black, 100/pkg



Download drawing



Download spec sheet

Base Data

Local Order Number REL50L0C2

Type REL50L

Color Black (BK)

Features and Benefits

- Special design offers a release feature for quick and easy access to wire bundles.
- Head design provides high tensile strength even after repeated use; providing additional longevity.

Product Description HellermannTyton releasable cable ties offer a release feature in the head allowing for easy access to wire bundles when changes are necessary. The head design guarantees high tensile strength even after repeated use. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description Releasable Cable Tie, 9.8" Long, 50 lb Tensile Strength, PA66, Black, 100/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 50.0 lbs

Minimum Tensile Strength (Metric) 225.0 N

Length L (Imperial) 9.8 "

Length L (Metric) 250 mm

Fixation Method None

Identification Plate Position none

Releasable Closure Yes

Tie Closure plastic pawl

Variant Outside Serrated

Width W (Imperial) 0.3 "

Width W (Metric) 7.4 mm

Cable Tie Width Max. (Imperial) 0.42 "

Cable Tie Width Max. (Metric) 10.7 mm

Height H2 (Imperial) 0.31 "

Height H2 (Metric) 7.8 mm

Bundle Diameter Min. (Imperial) 0.1 "

Bundle Diameter Min. (Metric) 2.5 mm

Bundle Diameter Max. (Imperial) 2.8 "

Bundle Diameter Max. (Metric) 70.0 mm

Logistics and Packaging

Quantity Per bag

Package Quantity (Metric) 100

Carton Quantity 5000

Material and Specifications

Material Polyamide 6.6 (PA66)

Material Shortcut PA66

Flammability UL94 V2

Operating Temperature -40°F to +185°F (-40°C to +85°C)

ROHS Compliant Yes