

T18RWPM9M4

Article Number: 126-00603

Arrowhead Wing Push Mount Tie, 4.5" Long, 18lb, Panel Thickness 0.19"-0.22", PA66, Natural, 1,000/pkg



Download spec sheet

Base Data

Local Order Number T18RWPM9M4
Type T18RWPM
Color Natural (NA)

Features and Benefits

- Easy and quick insertion ideal for production environment.
- Tie "clicks" into place upon final installation signaling installer insertion is complete.
- Arrowhead style mount provides low insertion and high extraction force.

Product Description Arrowhead Wing Push Ties design helps stabilize the tie in high vibration applications. This can be used on sheet metal, wood, and cast iron.

Short Description Arrowhead Wing Push Mount Tie, 4.5" Long, 18lb, Panel Thickness 0.19"-0.22", PA66, Natural, 1,000/pkg

Product Dimensions

Minimum Tensile Strength (Imperial) 18.0 lbs

Minimum Tensile Strength (Metric) 80 N

Length L (Imperial) 4.5 "

Length L (Metric) 113.0 mm

Fixation Method Arrowhead

Identification Plate Position none

Releasable Closure No

Tie Closure plastic pawl

Variant Inside Serrated

Width W (Imperial) 0.1 "

Width W (Metric) 2.5 mm

Width W2 (Imperial) 0.25 "

Width W2 (Metric) 6.4 mm

Height H (Imperial) 0.23 "

Height H (Metric) 5.8 mm

Bundle Diameter Min. (Imperial) 0.06 "

Bundle Diameter Min. (Metric) 1.5 mm

Bundle Diameter Max. (Imperial) 0.86 "

Bundle Diameter Max. (Metric) 22.0 mm

Disc Diameter (Imperial) 0.5 "

Disc Diameter (Metric) 13.1 mm

Panel Thickness Max. (Imperial) 0.13 "

| | | | |
|---|---------------|---|-------------------------------|
| Panel Thickness Max. (Metric) | 3.2 mm | | |
| Panel Thickness Min. (Imperial) | 0.06 " | | |
| Panel Thickness Min. (Metric) | 1.52 mm | | |
| Mounting Hole Diameter D (Imperial) | 0.19 - 0.22 " | | |
| Mounting Hole Diameter D (Metric) | 4.8 - 5.6 mm | | |
| Mounting Hole Diameter D Min. (Imperial) | 0.19 " | | |
| | | Mounting Hole Diameter D Max. (Imperial) | 0.22 " |
| | | | Thickness T (Imperial) |
| | | | 0.043 " |
| Mounting Hole Diameter D Max. (Metric) | 5.6 mm | | |
| | | Mounting Hole Diameter D Min. (Metric) | 4.8 mm |
| Thickness T (Metric) | 1.1 mm | | |

Logistics and Packaging

| | |
|----------------------------------|-------|
| Quantity Per | bag |
| Package Quantity (Metric) | 1000 |
| Carton Quantity | 10000 |

Material and Specifications

| | |
|--------------------------------------|----------------------------------|
| Material | Polyamide 6.6 (PA66) |
| Material Shortcut | PA66 |
| Flammability | UL94 V2 |
| Operating Temperature | -40°F to +185°F (-40°C to +85°C) |
| ROHS Compliant | Yes |
| Certification/Specification | UL |
| UL Listed (US and Canada) | No |
| UL Recognized (US and Canada) | Yes |