



PLAYMATE

Key Features:

- Compact 4u low noise audio design
- 4 Line control channels plus separate microphone section (Hi/Lo EQ)
- 2 phono/line, 6 stereo Line and 3 microphone inputs
- 3-band equalizer per channel (-30dB/+10dB)
- Replaceable assignable crossfader
- Stereo Master audio out on both RCA and balanced XLR
- Stereo (variable) Zone and PFL Zone output
- Master Panorama and Mono option
- High Output Headphone amplifier with Split/Blend mixing control
- Aux4 input on front (3.5mm mini jack for iPhone etc)
- Extremely clean signal-to-noise ratio

Specifications:

Inputs:

Line/Aux: 10Kohm input impedance, 77mV rms sensitivity for 1.22V output
 Mic: 600 ohm input impedance unbalanced, 1mv rms sensitivity for 1.22V output

Outputs:

Line: 9V rms max
 Headphone 0.5W into 47 ohm
 Power Supply: Switch Power AC 115-230V-50Hz
 Power Consumption: 12W typical, 21W with full headphone output

Dimensions:

Face Panel 483x177
 Rear Panel 434x80mm
 Depth 85mm including rubber feet
 Weight: 4KG

The player section:

- Select play from USB, SD (max 32GB) and Bluetooth
- Plays both WAV and MP3 files
- All, Single, Repeat and Random Play