

## DYMO

## **XTL™ 500**

#### 54 mm PC-Connected Touch Screen Industrial Label Maker

- Life-like on screen print preview and colour display shows exactly how labels will look when applied to cables, pipes, panels and more
- Built-in label applications make getting started from the home screen easy
- Touch screen helps make label creation easier and faster
- Pre-loaded label templates create labels 3x faster\* and ensure perfect formatting to save time
- Prints 6 mm to 54 mm durable labels including continuous length tape, laminated wire/cable wraps, heat-shrink tubes and pre-sized labels
- Maximised print area helps reduce label waste
- Pre-set layouts for almost 100 patch panel models eliminate size and spacing guesswork
- Easily transfer labels to and from DYMO ID software and the PC-connected\*\*
  XTL™ 500 for jobsite editing and printing
- Built-in auto-cutter for high volume label output
- · Impact-resistant rubber bumpers and wipe-clean keypad withstands harsh environments
- Customisable printer settings eliminate unnecessary menus and steps
- On-screen label indicator automatically detects and displays the loaded label

\*When compared to creating labels on an XTL label maker without templates

#### XTL 500 Case Kit Includes:

- DYMO XTL 500 Label Maker
- All-Purpose Vinyl Label Cartridge, Black on White, 54 mm x 7 m
- Laminated Wire/Cable Wrap, Black on White, 38 mm x 39 mm
- Carrying Case
- AC Charging Adapter
- USB Cable
- Rechargeable Lithium Polymer Battery
- Quick Start Guide
- Software Download Card





Quick Specs	
Unit Dimensions (H x W x L)	121.92 x 160.02 x 269.24 mm
Weight (excluding battery)	1.99 kg
PC Compatible	Yes, via USB
Accepts Label Sizes	6, 9, 12, 19, 24, 38, 51mm
Tape Platform	XTL
Resolution	300 dpi
Printing System	Thermal Transfer
Print Speed (average)	28 mm/sec
Barcodes	Code 128 (Auto), Code 39, Code 39 Mod 43, EAN 8, EAN 13, UPC-A, Codabar, PDF-417, QR Code
Cutter Type	Auto, Replaceable
Power Supply	Lithium Polymer Rechargeable Battery or AC Adapter
Memory	40 MB
Compatibility	Windows® 7 and later
Adapter	Yes
Warranty	3+1 Year Limited
Networking	No
Country of Origin	China







<sup>\*\*</sup>Works with Windows® 7 and later





### **XTL™ 500**

Item Number	Description		Length (mm)	Width (mm)	Height (mm)	Weight (kg)	QTY	EAN
1873306 DY XTL 500 PRINTER KIT QWERTY UK/IRE		Unit	408	144	365	5.05	1	3501178733068
	DY XTL 500 PRINTER KIT QWERTY	Shelf	440	320	400	9.19	1	-
	Case	440	320	400	11.01	2	13501178733065	
		Pallet	1200	800	950	157.08	12	-

#### **XTL 500 | Compatible Labels**

#### **All-Purpose Vinyl**

- · Moisture, chemical and UV resistance makes vinyl ideal for indoor/outdoor use
- · Wide range of colours that fit with OSHA, ANSI and ISO colour standards to enhance workplace communication and safety
- UL recognised as a component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 60°C

#### Flexible Cable Wrap

- For labelling wires, cables and rounded surfaces, flexible nylon material is designed to conform and stick
- Tear-proof material resists damage when pulled through tight spaces or conduits
- UL recognised as a component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 60°C

#### **Pre-Sized Safety Labels**

- Specific labels with colored headers including labels preprinted with DANGER and NOTICE headers for on-demand printing of small format safety signage
- · UL recognised as a component to UL 969
- RoHS compliant
- Temperature rating: -40°C to 60°C

#### **Laminated Wire/Cable Wraps**

- · Pre-sized wire/cable wraps with laminated overwrap protect printed areas from oil, chemicals, moisture, abrasion and fading
- · Also available in sheet label formats for high-volume installations
- UL recognised as a component to UL 969
- Temperature Rating: -40°C to 60°C

#### **Permanent Flat Surface**

- For labelling panels, blocks, faceplates, shelves, bins, beams and more
- · For labelling flat surfaces, a glossy finish leaves a professional look
- UL recognised as a component to UL 969
- Temperature rating: -40°C to 60°C
- RoHS compliant

#### **Heat-Shrink Tube (Continuous & Pre-Sized)**

- Heat-Shrink Tubes provide insulation when shrunk down and ensure a secure fit on wires and cables with a 3:1 shrink ratio
- Meets MIL-M-81531, MIL-STD-202G, SAE-DTL- 23053/5 (Class 1 & 3)
- UL recognised as a component to UL 224
- RoHS compliant
- Temperature rating: Max 125°C

#### **Pre-Sized Labels**

- · Ideal for flat surface labeling like barcodes, faceplates, shelves, bins, beams and more
- Pre-Sized labels help facilitate batch label printing to improve productivity
- UL recognised as a component to UL 969
- Temperature rating: -40°C to 60°C












# DYMO'

## **XTL™ 500**



SKU	Label Width	Label Length	Labels/Cartridge	Colour
re-Sized Labels				
1868665	12 mm	12 mm	250	А
1868666	12 mm	25 mm	250	А
1868667	12 mm	38 mm	185	А
1868668	25 mm	25 mm	250	А
1868669	9 mm	25 mm	250	А
1868670	12 mm	19 mm	250	А
1868701	19 mm	25 mm	250	А
1868702	25 mm	51 mm	100	А
1868703	51 mm	76 mm	100	А
.aminated Wire/Cable Wra	ар			
1868704	21 mm	21 mm	250	Α
1868705	21 mm	39 mm	150	Α
1868706	21 mm	102 mm	75	Α
1868707	38 mm	21 mm	250	А
1868708	38 mm	39 mm	150	Α
1868709	38 mm	102 mm	75	Α
1868710	51 mm	21 mm	250	Α
1868711	51 mm	39 mm	100	А
1868712	51 mm	102 mm	70	А



Newell Europe Sàrl Chemin de Blandonnet 10 1214 Vernier – Switzerland WWW.DYMO.COM

This information is being provided for general information purposes and the compliance standards and certifications referenced herein are based on current standards which are subject to change.









## **XTL**<sup>™</sup> **500**


SKU	Label Width	Label Length	Labels/Cartridge	Colour
e-Sized Heat-Shrink Tu	ıbe			
1868717	6 mm	34 mm	81	А
1868718	12 mm	34 mm	65	А
1868719	24 mm	34 mm	60	А
1868720	54 mm	34 mm	25	А
1868731	6 mm	47 mm	81	А
1868732	12 mm	47 mm	65	A
1868733	24 mm	47 mm	60	A
1868734	54 mm	47 mm	25	A
e-Sized Safety Labels	(with coloured headers)			
1868713	51 mm	102 mm	70	
1000713	51 111111	102 111111	70	А
1868714	51 mm	102 mm	70	
1000714	31 111111	102 111111	70	A
1868715	51 mm	102 mm	70	NOTICE
1000713	JI IIIII	102 111111	70	Α
1868716	51 mm	102 mm	70	<b>▲</b> DANGER





DISTRIBUTED BY: Newell Europe Sàrl Chemin de Blandonnet 10 1214 Vernier – Switzerland WWW.DYMO.COM









## **XTL**<sub>™</sub>**500**

Part Number table – Language / Keyboard Type:

DYMO XTL 500 54mm Label Maker Kit, QWERTY, UK/IRE - 1873306

DYMO XTL 500 54mm Label Maker Kit, QWERTZ, DE/AT/CH - 1873309

DYMO XTL 500 54mm Label Maker Kit, AZERTY, FR/BE – 1873482

DYMO XTL 500 54mm Label Maker Kit, QWERTY, SEU+NL - 1873489





