

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [1054500101](#)  
**Status:** **Active**  
**Overview:** [Consumer USB Products](#)  
**Description:** Universal Serial Bus (USB) Shielded I/O Receptacle, Type C, Right Angle, Surface Mount, Gold (Au) Flash over 0.76µm Palladium Nickel Plating

**Documents:**

[3D Model](#) [Product Specification PS-105448-001 \(PDF\)](#)  
[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**


Product Family	I/O Connectors
Series	<a href="#">105450</a>
Application	Wire-to-Board
Comments	Nickel underplating
Component Type	Receptacle
Overview	<a href="#">Consumer USB Products</a>
Product Name	USB 3.1
Type	C
UPC	889056497121

**Physical**

Circuits (Loaded)	24
Circuits (maximum)	24
Color - Resin	Black
Durability (mating cycles max)	10000
Gender	Receptacle
Keying to Mating Part	None
Lock to Mating Part	Yes
Material - Metal	Copper Alloy
Material - Plating Mating	Gold over Palladium Nickel
Material - Plating Termination	Gold
Material - Resin	High Temperature Thermoplastic
Net Weight	0.539/g
Number of Rows	2
Orientation	Right Angle
PCB Locator	Yes
PCB Retention	None
PCB Thickness - Recommended	0.70mm
Packaging Type	Embossed Tape on Reel
Panel Mount	Yes
Pitch - Mating Interface	0.50mm
Pitch - Termination Interface	0.50mm
Plating min - Mating	0.051µm (Au), 0.762µm (PdNi)
Plating min - Termination	0.051µm
Polarized to Mating Part	No
Polarized to PCB	Yes
Ports	1
Surface Mount Compatible (SMC)	Yes
Temperature Range - Operating	-30°C to +85°C
Termination Interface: Style	Surface Mount

**Electrical**

Current - Maximum per Contact	0.25A, 1.25A, 5.0A
Grounding to Panel	None
Shield Type	Full Shield
Shielded	Yes



*Series image - Reference only*

**EU ELV**

**Not Reviewed**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Reviewed

**Halogen-Free**

**Status**

**Not Reviewed**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

Not Reviewed

ELV

Not Reviewed

**Search Parts in this Series**

[105450](#) Series

**Mates With**

USB Type C Plug/Cable

Voltage - Maximum

30V AC/DC

**Material Info**

**Reference - Drawing Numbers**

Product Specification

PS-105448-001

Sales Drawing

SD-105450-001

This document was generated on 03/09/2016

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**