

Digimatic Height Gage Series 192-Standard Type with SPC Data Output

Series 192

FEATURES

- Easy-to-use standard type.
- Carbide-tipped scriber is provided.
- Double-column structure ensures high measuring accuracy.
- With SPC data output.

Technical Data

Accuracy: Refer to the list of specifications.
 Resolution: 0.01mm or .0005"/0.01mm
 Display: LCD, 7-digit character height 11mm
 Max. response speed: 500mm/s
 Battery: SR44(1pc.), 938882
 Battery life: Approx. 2000 hours under normal use

Function

Zero-setting, ABS/INC switching, Two presets, Probe tip diameter compensation-/+ switching,
 Power ON/OFF, Data hold,
 inch/mm conversion (on inch/mm models only)
 Alarm: Low voltage, Counting value composition error

Standard Scriber Provided

Metric models: Carbide-tipped scriber (07GZA000) and scriber clamp (05GZA033)
 Inch/Metric models: Carbide-tipped scriber (07GZA000) and scriber clamp (05GZA033)
 and scriber clamp 901385)

Optional Accessories

953638: Holding bar for test indicator (length: 50mm)
 900209: Holding bar for test indicator (length: 100mm)
 953639: Holding bar for test indicator (length: 2")
 900306: Holding bar for test indicator (length: 4")
 900321: Swivel clamp used with holding bar (metric)
 900322: Swivel clamp used with holding bar (inch)
 905338: SPC Cable (CD TYPE) 1M
 905409: SPC Cable (CD TYPE) 2M
 905691: 905691 CD/Connecting Cable L-Type 1M RIG
 905692: CD/Connecting Cable L-Type 2M RIG



Inch/Metric	Metric				
Order Number	192-630-10	192-631-10	192-632-10	192-633-10	
Image		-			
Parts	 Parts Break Down	 Parts Break Down	 Parts Break Down	 Parts Break Down	
Measuring Range	0-12in 0-300mm	0-18in 0-450mm	0-24in 0-600mm	0-40in 0-1000mm	
Accuracy	.001	.002	.002	.003	
Resolution	.0005in 0.01mm [.0002in(0.005mm)Switchable]	.0005in 0.01mm [.0002in(0.005mm)Switchable]	.0005in 0.01mm [.0002in(0.005mm)Switchable]	.0005in 0.01mm [.0002in(0.005mm)Switchable]	
Mass	4.7kg	7.5kg	8.3kg	15.7kg	