

Quick-Set Test Indicators - Series 513

Series 513

FEATURES

- Anti-magnetic
- Jeweled bearings
- No-clutch structure
- Water and dust resistant
- Glare-free crystal with scratch-resistant coating
- Metric dial faces in yellow
- The most direct gear train design ever applied to Test Indicators means—higher level of sensitivity, reliability, repeatability and accuracy throughout tool life.



Inch	Inch/Metric	Metric													
Order Number	513-282	513-402	513-402T	513-403	513-403T	513-412	513-412T	513-452	513-452T	513-453	513-453T	513-462	513-463	513-982	
Image	-	-	-	-	-		-	-	-		-	-	-	-	
Parts Break Down	-	-	-	-	-	-	-	-	-	-	-	-	-	-	
Accuracy	.0005in	0.0005in	0.0005in	0.0001in	0.0001in	0.0005in	0.0005in	0.0005in	0.0005in	0.0001in	0.0001in	0.0005in	0.0001in	0.0005in	
Dial Reading	0-15-0	0-15-0	0-15-0	0-4-0	0-4-0	0-15-0	0-15-0	0-15-0	0-15-0	0-4-0	0-4-0	0-15-0	0-4-0	0-15-0	
Graduation	.0005in	0.0005in	0.0005in	0.0001in	0.0001in	0.0005in	0.0005in	0.0005in	0.0005in	0.0001in	0.0001in	0.0005in	0.0001in	0.0005in	
Measuring Force	0.3N or less	0.3N or less	0.3N or less	0.3N or less	0.3N or less	0.3N or less	0.3N or less	0.3N or less	0.3N or less	0.3N or less	0.3N or less	0.3N or less	0.3N or less	0.3N or less	
Range	.03-in	0.03-in	0.03-in	0.008-in	0.008-in	0.03-in	0.03-in	0.03-in	0.03-in	0.008-in	0.008-in	0.03-in	0.008-in	0.03-in	
Remarks	-	-	-	-	-	Long Point	Long Point	-	-	Mini-Dial	-	Mini-Dial	Mini-Dial	-	
Type	Parallel	Horizontal	Horizontal	Horizontal	Horizontal	Horizontal	Horizontal	Vertical	Vertical	Vertical	Vertical	Horizontal	Horizontal	Parallel	

Pages: [1](#)