



MATERIALS:

High conductivity copper.
Finish: Tin plated

RATINGS:

Current: 15 Amperes

ORDERING INFORMATION: Model 5531

All dimensions are in inches. Tolerances (except noted): .xx = $\pm .02$ " (.51 mm), .xxx = $\pm .005$ " (.127 mm).
All specifications are to the latest revisions. Specifications are subject to change without notice.
Registered trademarks are the property of their respective companies.

Made in USA