

## CHERRY DW 3000



Models may vary from the image shown

### Professional wireless desktop for beginners

CHERRY DW 3000 is rock-solid CHERRY technology with an excellent price/performance ratio. Modern, flat design with gentle, quiet and durable wear-resistant keys. Universal, reliable and optimised for professional use.

### Key benefits

- Flat, wireless keyboard including cursor and number pad
- Whisper keystroke keys with wear-resistant laser key legends
- Up to 10 million keystrokes
- 4 hotkeys (calculator, e-mail, browser, sleep mode)
- Plug & Play via USB connection
- 3-button mouse, for both left-handed and right-handed operation
- Optical sensor technology (1,200 dpi)
- Battery status display in keyboard and mouse
- Almost interference-free wireless 2.4 GHz technology (range of up to 10 metres)
- Nano USB receiver
- GS approval

### Technical Data:

#### Layout (country or language):

Product dependant, see table "Models"

#### Housing colour:

black

#### Key colour:

black

#### Weight (product):

502 g (keyboard with battery), 85 g (mouse with battery), 1.5 g (receiver)

#### Total weight (with packaging):

923 g

#### Transmission range:

approx. 10 m

#### Frequency range:

2.400 GHz - 2.4835 GHz

#### Storage Temperature:

-20°C to 65°C

#### Operating Temperature:

0°C to 50°C






#### Current Consumption:

typ. 3 mA (keyboard), typ. 6 mA (mouse), max. 35 mA (receiver)

#### Interface:

- USB

#### Product approvals:

- c-tick 
- UL 
- CE 
- FCC 
- TÜV-Süd/GS 

#### System requirements:

- USB connection

#### Delivery Volume:

- Operating instructions in hard copy
- 1 battery (type AA)
- 1 optical wireless mouse
- 1 wireless keyboard
- 1 nano USB transmission receiver
- 1 battery (type AAA)

#### Dimensions (product):

458 x 170 x 20 mm (keyboard), 109 x 62 x 37 mm (mouse), 18 x 13 x 5 mm (receiver)

#### Packaging dimensions:

549 x 200 x 45 mm

#### Reliability:

- MTBF > 45,000 hours

#### Mouse:

- Scanning: Infrared
- Resolution: 1200 dpi
- Number of Keys: 3
- Mouse wheel design: Scroll wheel with key function
- Design: Symmetrical
- Connection: wireless
- Scanning rate: max. 2400/s
- Housing colour: anthracite
- Key colour: black

#### Keyboard:

- Key technology: LPK
- Service life, standard key: > 10 million key operations
- Number of Keys: Product dependant, see table "Models"
- Number of additional keys: 4

#### Packaging Unit:

- Number of products in the master package: 6
- Number of master packages per pallet: 21

#### Warranty:

2 years

Errors, technical changes and delivery possibilities excepted.  
Technical information refers only to the specifications of the  
products. Features may differ from the information provided.

## Models:

(possible country/layout versions, others available on request)

	Product name	Order number	EAN code	Layout (country or language)	Number of Keys
1	CHERRY DW 3000	JD-0700DE-2	4025112081378	Germany	105+4
2	CHERRY DW 3000	JD-0700EU-2	4025112081859	US English with EURO symbol	104+4
3	CHERRY DW 3000	JD-0700FR-2	4025112081385	France	105+4
4	CHERRY DW 3000	JD-0700GB-2	4025112081392	UK	105+4