ENN05002

Mureva BOX - junction box - 4 grommets Ø 20 - 65x65x45 mm







Main

Product range	Mureva BOX
Product type	Junction box
Colour	Grey RAL 7035
Quantity per package	5 pieces

Complementary

Mounting	Surface	
Cable entry	Grommets	
Fixing mode	Clip-on cover	
Interior dimensions	65 x 65 x 45 mm	
Number of cable entries	4 grommets Ø 20 mm	
Material	SBS (styrene butadiene styrene) grommet PP (polypropylene) cover ABS (acrylonitrile butadiene-styrene) body	
Electrical insulation class	Class II according to IEC 536	
Height	45 mm	
Width	88 mm	
Depth	88 mm	

Environment

Operating temperature	-2540 °C
IK-Class	IP55 according to IEC 60529
IK-Class	IK07 according to EN 50102
Glow wire temperature	650 °C
Standards	EN 60670
Product certifications	CE
Environmental characteristic	Halogen free

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 1026 - Schneider Electric declaration of conformity
REACh	Reference not containing SVHC above the threshold
Product environmental profile	Available
Product end of life instructions	Need no specific recycling operations