




ELECTRICAL TEST:


100% simulated test using computer

Pin Assignment


	P1		P2
CC	A5	Brown	A5
DP1	A6	GREEN	A6
DN1	A7	WHITE	A7
SBU1	A8	BLUE	A8
Vconn	B5	YELLOW	B5
SBU2	B8	ORANGE	B8
SSTXp1	A2	Brown	A2
SSTXn1	A3	WHITE	A3
		Drain	
SSRXp2	A11	RED	A11
SSRXn2	A10	WHITE	A10
		Drain	
SSTXp2	B2	GREEN	B2
SSTXn2	B3	WHITE	B3
		Drain	
SSRXp1	B11	BLUE	B11
SSRXn1	B10	WHITE	B10
		Drain	
GND (A1,A12,B1,B12)			A1,A12,B1,B12 BLACK
Shell			Shell
VBUS (A4,A9,B4,B9)			A4,A9,B4,B9 RED

15	SCREW #4-40UNC H4.75*8.6MM Ni PLATED	2	PCS
14	C+VGA+USB ABS HSG White No Mark	1	PCS
13	UTC-CUV01(VL100) PCB, Connector Terminal PIN GOLD PLATED:G/F,Shell: Ni PLATED	1	PCS
12	USB3.1 Dongle Wire clamp,10PIN Material:NY-66+15%GF	1	PCS
11	C+VGA+USB White ABS HSG Size:80*14.5*40mm Mark: 	1	PCS
10	LD-PE TRANSPARENT	3	G
9	USB3.1 TYPE-C Wire clamp Material:NY-66+15%GF	1	PCS
8	USB3.1 TYPE C Bottom Shell	1	PCS
7	USB3.1 TYPE C Top Shell	1	PCS
6	OD:1.5mm Black Heat Shrink Tube	0.02	M
5	USB3.1 TYPE C ABS HSG White	1	PCS
4	USB3.1 TYPE C ABS HSG White No Mark	1	PCS
3	45P White PVC	12	G
2	USB3.1 C Type Connector With,Terminal PIN GOLD PLATED:G/F,Shell: Ni PLATED	1	PCS
1	USB 3.1~UL2725~[34AWG(7/0.06TC)+EAM]*4P+34AWG(7/0.06TC)*2C +28AWG(7/0.127)*2C+AB(16/9/0.06TC 70%TC)OD:3.9MM~White	0.17	PCS
NO	DESCRIPTION	Q'TY	UNIT

REV.	ECN No.:		DESCRIPTION		DATE	NAME
	TOLERANCE INCHES M/M					
	.X	.015	.30			
	.XX	.010	.10			
	.XXX	.005	.05			
TITLE:				UTC-CUV01(TYPE CM To CF+VGA F+USB3.0 AF)		
DRAWN BY	Jerry.Liu		CUSTOMER :		Element 14	
CUSTOMER P/N :			CS29290(PSG91235)			
CHECK BY			SCALE	NONE	DRAWING NO.:	REV. A01
APPD BY			UNIT	MM		1/2
			DATE	15.12.03		




Shipping Mark




Side Mark

P/O NO.:	
ITEM NO.:	
DESCRIPTION:	
Q'TY	PCS
N.W:	KGS
G.W:	KGS
MEAS:	50X32X21CM



1PCS Packing/Zip-PE BAG



MATTERS NEED ATTENTION:

1. Put a waterproof bag In the carton, Every carton xxxPCS.
2. Top and bottom put a cardboard, sealed by clear tape.

NO		DESCRIPTION	Q'TY	UNIT
5	Label	black type on White Label Size:50*20mm	1	PCS
4	Waterproof	Waterproof Bag:850*750*0.06MM	1/xxx	PCS
3	Pasteboard	Pasteboard:480*300MM B3C	2/xxx	PCS
2	Carton	Carton Size:50X32X21CM K=K mark:MCM...	1/xxx	PCS
1	PE Bag	PE Bag SIZE:100*200*0.06mm	1	PCS
NO		DESCRIPTION	Q'TY	UNIT

REV.	ECN No.:	DESCRIPTION	DATE	NAME
		TOLERANCE INCHES M/M		
.X	.015	.30		
.XX	.010	.10		
.XXX	.005	.05		
		TITLE: UTC-CUV01(TYPE CM To CF+VGA F+USB3.0 AF)		
DRAWN BY	Jerry.Liu	CUSTOMER :	Element 14	
CHECK BY		CUSTOMER P/N :	CS29290(PSG91235)	
APPD BY		SCALE	NONE	REV. A01
		UNIT	MM	
		DATE	15.12.03	2/2