


**Fuse terminal block; for class CC fuses; without blown fuse indication; suitable for DIN 35 rail acc. to EN 60715; 3-pole**

Item No.: 811-430



Fuse terminal block; for class CC fuses; without blown fuse indication; suitable for DIN 35 rail acc. to EN 60715; 3-pole

### Marking

RoHS ✓  
Compliant

### Business data

Supplier	WAGO
Item no.	811-430
GTIN / EAN	4050821508182
Content	1
Order amount	1
Customer item number	

### Notes

### Technical data

#### Miscellaneous

No. of poles	3
Total number of connection points	6
Total number of potentials	3
Color	light gray
Ratings according to 1	IEC/EN 60947-7-3
Nominal current [A]	32 [A]
Connection technology (1)	CAGE CLAMP®
Solid sizes 1	2.5 ... 16 mm <sup>2</sup> / 16 ... 6 AWG

Printview: Fuse terminal block; for class CC fuses; without blown fuse indication; suitable for DIN 35 rail acc. to EN 60715; 3-pole - Item No.: 811-430

<b>Technical data</b>	
<i>Fine-stranded wires 1</i>	<i>2.5 ... 16 mm<sup>2</sup> / 16 ... 6 AWG</i>
<i>Strip length 1</i>	<i>12 ... 13 mm / 0.47 ... 0.51 in</i>
<i>Type of wiring</i>	<i>Front-entry wiring</i>
<i>Design</i>	<i>horizontal</i>
<i>Insulating material</i>	<i>Polyamide 66 (PA 66)</i>
<i>Weight [g]</i>	<i>1.111 [g]</i>
<i>Width</i>	<i>52.5 mm / 2.067 in</i>
<i>Height from upper-edge of DIN-rail [mm]</i>	<i>55 [mm]</i>
<i>Height from upper-edge of DIN-rail</i>	<i>55 mm / 2.165 in</i>
<i>Length</i>	<i>105 mm / 4.134 in</i>
<i>Type of mounting</i>	<i>DIN 35 rail</i>
<i>Safety information 1</i>	<i>Electrical ratings are given by the fuse.</i>
<i>Safety information 2</i>	<i>Temperature scale handling from -35°C ... +85°C</i>

Images & drawings



**Address**

WAGO Kontakttechnik GmbH & Co. KG

Hansastr. 27

32423 Minden

Telefon: 0571/887-0

Fax: 0571/887-169

<http://www.wago.com>

© WAGO Kontakttechnik GmbH & Co. KG

Technische Änderungen und Irrtümer vorbehalten.