



CABLE STRIPPER

CABLE STRIPPER

Cat No: 52040895

UPC No: 783310126799

Description

- Triple action stripping - rotary, linear, and spiral - Window stripping is accomplished by combining 2 rotary cuts with a spiral cut in between them
- Eliminates Cable Scoring.
- Blade height is adjustable to precisely match insulation thickness
- Interchangeable cable guides for small and large cable diameters
- Hook on the cable guide is used to start jacket removal without the need to use a screwdriver or pliers
- Replacement blade storage pocket in the base of the tool
- Long life, high-carbon steel blade
- Ergonomic handle shape
- Suitable for most jacket materials

Specifications

- Capacity :
 - THHN Cable Size Range: 8 AWG - 1250 KCMIL (10.000 - 625.000MM²), Overall Cable Diameter: 0.180 - 1.570 IN (4.500 - 40.000 MM), Cable Diameter Using Small Cable Guide Hook: 0.180 - 0.980 IN (4.500 - 25.000 MM)
 - Cable Diameter Using Large Cable Guide Hook: 0.79" to 1.57" (20.0-40.0mm)
- Handle Type : Ergonomic
- Material : High Carbon Steel Blade
- Replacement Part : 13544 Replacement Blade (2 Per Package)
- Weight : 0.250 LB (0.100 GM)