



## **RC09X**

### Variable Speed 9.6v Rotary Tool Kit

A 9.6v compact, rechargeable cordless tool with variable speed and LED spotlight feature for close-up work

- 9.6v variable speed re-chargeable rotary tool
- 100 accessories including collets 1,2.35,3 & 3.2m
- 8000-20,000rpm variable speed
- Up to 35 minutes use between charges! 2-3 hours charge
- Two grip positions- Pen & palm grip
- Additional LED spotlight feature for lighting dark areas
- Handy padded zip bag & a 1 x 9.6v DC Ni-MH battery
- Hanging hook
- Includes both UK & EU charging adaptor

### **Features & Benefits**

- 9.6v variable speed rotary tool
- 8000- 20,000rpm variable speed
- Two grip positions- Pen & Palm
- Additional LED spotlight feature for lighting dark areas
- 100 accessories including collets 1,2.35,3 & 3.2m
- Hanging hook
- Includes both UK & EU charging adaptor
- The compact size means that work can be carried out in tight spaces where larger tools will not reach.
- Ideal for tasks where freedom and flexibility are required

### **Technical specifications:**

- 9.6v DC Ni-MH battery
- In-built speed control
- Cordless power 9.6v fan cooled motor
- Up to 35 minutes use between charges! 2 -3 hours
- Charging station- 230v/50Hz
- Includes both UK & EU charging adaptor

### **Accessories**

100 pcs accessories including:

- 4 x Collet chucks (sizes 1.00,2.35,3.00,3.20 diameter)
- 4 x Drill bits (sizes 1.00, 2.35, 3.00, 3.20 diameter)
- 1 x Polishing wheel shank

- 2 x Big fleece polishing wheels (22x6mm)
- 2 x Small fleece polishing wheels (9x6mm)
- 20 x Diamond points
- 10 x Grinding stones
- 2 x Mandrels with screw top
- 18 x Carborundum cutting wheels (22mm diameter)
- 18 x Sanding discs (20mm diameter)
- 2 x Sanding drum mandrels
- 4 x Sanding drums (13 x 13mm diameter)
- 4 x Sanding drums ( 6 x 13mm diameter)
- 6 x Wire wheel brushes (Brass & Steel)
- 3 x Nylon pencil brushes