

Product data sheet

Description: High Power LCD Rotary Tool Kit

Product Code: RC250X

Detail: High power and exact digital speed setting ideal for precision hobby & small DIY, repair or restoration jobs

Features & Benefits:

- 230v variable speed rotary tool
- Hanging hook
- Button LCD speed control 8000-35,000 rpm
- 2 grip positions-pen & palm with comfortable soft grip
- 100 accessories including collets 1.0, 2.35, 3.0, 3.2mm
- Ideal for tasks where both power and precision are required

Technical specifications:

- 170W Rotary tool kit
- On/off switch
- Powerful 230v fan cooled motor
- Variable speed with digital LCD display & high quality bearings for smoother running
- 2m cable
- EUK plug- suitable for EU and UK countries

Accessories

- 100 pcs accessories including:
- 4 x Collet chucks (sizes: 1.00, 2.35, 3.00, 3.20 diameter)
- 4 x Drill bits (sizes: 1.00, 2.35, 3.00, 3.20 diameter)
- 1 x Polishing wheel shank
- 2 x Big fleece polishing wheels (22x6mm)
- 2 x Small fleece polishing wheel (9x6mm)
- 20 x Diamonds points
- 10 x Grinding stones
- 2 x Mandrel with screw tops
- 20 x Carborundum cutting wheels (22mm diameter)
- 20 x Sanding discs (20mm diameter)
- 2 x Sanding drum mandrels
- 3 x Sanding drums (13x13mm diameter)

shesto™

- 3 x Sanding drums (6 x 13mm diameter)
- 6 x Wire wheel brushes (brass & steel)
- 1 x Nylon pencil brush