



## KIT LAN PRO-NAVIGATOR

LAN ProNavigator test set (main & remote)

Cat No: 52051666

UPC No: 769328108170

### Description

---

- Simple PASS/FAIL test results in one second allows technicians to quickly move on to the next test site
- Generates oscillating audio tone for use with tone probes to locate cables
- Tests data and telephone cables up to 320 feet (100 meters) for proper pairing for EIA/TIA-568A, EIA/TIA-568B, Token Ring, 10 Base T, and common Category 5 configurations
- Tests unshielded UTP and shielded STP data cable
- Detects good connections, open connections, crossed wires and split pairs
- Tests common BNC connected 50 and 75 ohm coaxial cables up to 320 feet (100 meters) for continuity
- Tests coaxial cable types RG58, RG59, RG6, RG6 Quad, Belden 8281, RG8, RG11 and more
- Belt clips provided and lanyard holes embedded in case to attach to belt or wrist
- Features low battery test and auto-off function to preserve battery life
- Includes standard 9V battery

### Specifications

---

- Includes :
- 2 RJ45 Patch Cords
- 2 BNC Coaxial Cables
- 2 CATV F To BNC Adapters
- 1 BNC/BNC Adapter
- 1 Shielded RJ45 Coupler
- 2 Belt Clips In Durable Case
- Size : 8.500 IN (216.000 MM) x 7.600 IN (193.000 MM) x 3.000 IN (76.000 MM)
- Sub Brand : LAN ProNavigator
- Weight : 2.000 OZ (1140.000 G)