



**GREENLEE.**  
A Textron Company

MADE FOR THE TRADE!™



CLAMP METER, TRUE RMS AC (CM-450)

AC Clamp-on Meter, True RMS

Cat No: 52033579

UPC No: 783310127260

### Description

---

- AC amperage, AC/DC voltage measurement
- True RMS for the most accurate measurement where harmonics are present
- Quick, easy operation
- Auto power off for longer battery life
- Resistance measurement
- Audible continuity and diode tests
- Frequency measurement
- Data hold to capture measurement
- 4000 count LCD
- Accessories included: Test leads, 3V Standard button battery (IEC-CR 2032; ANSI-NEDA 54004LC)
- Lifetime Limited Warranty

### Specifications

---

- Amperage Measurement : 40, 400, 600 A AC
- Display : LCD, 4000 Count
- Includes : 3 V Standard Button Battery, Test Leads
- Jaw Opening : 1.020 IN
- Measurement Category : CAT III, 600 V Per UL 61010-1
- Replacement Part : TSG-3 Sure-Grip Test Leads, TC-5 Carrying Case
- Resistance Measurement :
  - 400 $\Omega$ ;
  - 4, 40, 400k $\Omega$ ;
  - 4, 40M $\Omega$ ;
- Standard : CAT III, C/US UL Listed, CE
- Type : AC, TRMS
- Voltage Measurement :
  - 4, 40, 400, 600 V AC
  - 4, 40, 400, 600 V DC
  - 400 mV