

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

0192120005

Status:

Active

Overview:

Wire Pins

Description:

InsulKrimp™ Wire Pin Terminal for 16-14 AWG Wire

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

Agency Certification

CSA	LR18689
UL	E32244

General

Product Family	Crimp Terminals
Series	19212
Application	Power
Comments	Pin Length 9.40mm
Crimp Quality Equipment	Yes
MolexKits	Yes
Overview	Wire Pins
Packaging Alternative	19212-0006 (Adhesive Tape on Reel)
Product Name	Wire Pin
UPC	800753053366

Physical

Flammability	94V-0
Gender	Male
Material - Metal	Copper
Material - Plating Mating	Tin
Net Weight	0.780/g
Packaging Type	Bag
Plating min - Mating	1.016µm
Termination Interface: Style	Crimp or Compression
Wire Insulation Diameter	4.45mm max.
Wire Size AWG	14, 16
Wire Size mm²	N/A

Material Info

Old Part Number	WP-2614X
-----------------	----------

Reference - Drawing Numbers

Sales Drawing	SD-19212-001
---------------	--------------



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

Compliant

China RoHS

REACH SVHC

Not Contained Per -
ED/21/2016 (20 June
2016)

Halogen-Free

Status

Not Low-Halogen

Need more information on product
environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any
non-product compliance questions.

China ROHS	Green Image
ELV	Not Relevant

Search Parts in this Series

19212 Series

Application Tooling | FAQ

Tooling specifications and manuals are
found by selecting the products below.
Crimp Height Specifications are then
contained in the Application Tooling
Specification document.

Global

Description	Product #
PremiumGrade™	0640010100
Hand Crimp Tool	
Hand Crimp Tool	0640010300
Crimp Head for the	0640050100
AT-200™ Pneumatic	
Hand Tool	
Crimp Head for the	0640050300
AT-200™ Pneumatic	
Hand Tool	

This document was generated on 07/18/2016

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION