

## STANDARD PUSHBUTTONS (Cont.)



Retail Part No.	Bulk Part No.	Fig. No.	Circuit Function	Poles/Throws	Amps 125 VAC	Amps 250 VAC	Bushing Length	Actuator Length	Actuator Color/Material	Frame/Bezel	Terminal Type	Mount Hole	Hardware	Spec. Drawing Page No.
35-3454	35-3454-BU	1	On Off	SPST††	10*	N/R	0.561	0.410	Chrm. Metal		6" WL	0.500	N, KN	265-A
35-473	35-473-BU	2	NO/ NC	SPDT	16†	16†	0.380	0.125	Red Plastic	Black Shroud	QC .250"	0.500	N	265-B
35-458	35-458-BU	3	On Off	SPST	15	10	0.562	0.238	Chrm. Metal		Sc	0.500	N, KN, Sc	265-C
35-3425	35-3425-BU	4	On Off	SPST	15	10	0.561	0.415	Chrm. Metal		Sc	0.500	N, KN, Sc	265-D
35-3427	35-3427-BU	4	Off (On)	NO SPST	15	10	0.561	0.415	Chrm. Metal		Sc	0.500	N, KN, Sc	265-D
35-3429	35-3429-BU	4	On (Off)	NC SPST	15	10	0.561	0.415	Chrm. Metal		Sc	0.500	N, KN, Sc	265-D
35-3490	35-3490-BU	4	On On	SPDT	15	10	0.561	0.415	Chrm. Metal		Sc	0.500	2 N, Sc	265-D
35-455	35-455-BU	5	Off On	SPST	16^	16	Snap-in	0.157	Red Plastic	Black	QC .250"/Sd	0.992		265-E
35-457	35-457-BU	5	Off (On)	NO SPST	16^	16	Snap-in	0.157	Red Plastic	Black	QC .250"/Sd	0.992		265-E
35-459	35-459-BU	5	Off (On)	NO SPST	16^	16	Snap-in	0.157	Black Plastic	Black	QC .250"/Sd	0.992		265-E
35-490	35-490-BU	6	On Off	DPDT††	8	6	0.730	0.312	OrangeΔ	Black	PCB/Sd Lug	0.530	N, W	265-F
35-3484	35-3484-BU	7	Off (On)	NO SPST	****	****	1.200	0.375	Black Chrome	Black	Sc	0.625	N, W	265-G

Notes: (On)/(Off)/(SPDT)=Momentary Action  
 \*Rated 8Amps @125V DC, 4Amps @250V DC, 1/3 HP @125VAC;  
 \*\*Rated 6Amps @120VAC/3Amps @240VAC  
 \*\*\*Rated 3Amps @120VAC/1.5Amps @277VAC  
 \*\*\*\*Rated (25, 15) Amps @ (6,12) VDC  
 ^=1/2 HP @ 125VAC, 1 HP @ 250 VAC  
 †=Rated 1/2 HP @125 VAC, 0.2A @250 VDC

††=Alternate Action  
 Chrm.=Chrome  
 HP=Horse Power  
 35-490 comes with Nut and Washer Hardware  
 35-490 pin can be removed to make momentary  
 Δ=Mechanical Indicator, non-illuminated

NC=Normally Closed  
 NO=Normally Open  
 N/R=Not Rated  
 QC=Quick Connect  
 Sc=Screw

Sd=Solder  
 W=Washer  
 WL=Wire Lead  
 KN=Knurled Nut  
 N=Nut(s)

## LIGHTED PUSHBUTTONS



### Switches

Retail Part No.	Bulk Part No.	Fig. No.	*Circuit Function	Poles/Throws	Amps 125 VAC	Amps 250 VAC	Amps 14 VDC	HP 125 VAC	Bushing Length	Actuator Length	Actuator Color	Actuator Style	Terminal Type	Mounting Hole	Spec Drawing Page No.
35-480	35-480-BU	8^	On Off	SPST	10	10	10	1/4	Snap-in	0.360	Red Lens	Square	QC .25"/Sd	1.10 x 0.88	265-J
35-481††		8									Red Lens	Square			265-J
35-482	35-482-BU	8^	On Off	SPST	10	10	10	1/4	Snap-in	0.360	Amber Lens	Square	QC .25"/Sd	1.10 x 0.88	265-J
35-484	35-484-BU	8^	On Off	SPST	10	10	10	1/4	Snap-in	0.360	Green Lens	Square	QC .25"/Sd	1.10 x 0.88	265-J
35-3412	35-3412-BU	9	(1NC)(1NO)	SPDT		4†			0.295	0.196		Square	Sd Eyelet	0.638	265-H
35-3414	35-3414-BU	9	1NC 1NO	SPDT		4†			0.295	0.196		Square	Sd Eyelet	0.638	265-H
35-3430	35-3430-BU	9	2NC 2NO	DPDT		4†			0.295	0.196		Square	Sd Eyelet	0.638	265-H
35-3431	35-3431-BU	10	2NC 2NO	DPDT		4†			0.295	0.196		Rq	Sd Eyelet	0.638	265-I
35-3432	35-3432-BU	10	(1NC)(1NO)	SPDT		4†			0.295	0.196		Rq	Sd Eyelet	0.638	265-I

### Lens and Diffuser Kits

Choose a Lens and Diffuser Kit below to go with Fig. 9 and Fig. 10 above part numbers (Sold Separately)

Retail Part No.	Bulk Part No.	Figure No.	Style	Color	Spec Drawing Page No.	Retail Part No.	Bulk Part No.	Figure No.	Style	Color	Spec Drawing Page No.
35-3435	35-3435-BU	11	Square	Green	265-K	35-3440	35-3440-BU	12	Rectangle	Green	265-L
35-3437	35-3437-BU	11	Square	Red	265-K	35-3442	35-3442-BU	12	Rectangle	Red	265-L
35-3438	35-3438-BU	11	Square	Clear	265-K	35-3443	35-3443-BU	12	Rectangle	Clear	265-L
35-3439	35-3439-BU	11	Square	Yellow	265-K	35-3444	35-3444-BU	12	Rectangle	Yellow	265-L
	35-3400-BU		12V Replacement Bulb				35-3400-BU		12V Replacement Bulb		

Notes: ( )=Momentary Function  
 \*NC=Normally Closed and NO=Normally Open  
 ^=12V Incandescent

N/R=Not Rated  
 PCB=Printed Circuit Board  
 †=0.2A @ 220VDC, 5mA @ 12VAC/DC

††=Lens Only  
 QC=Quick Connect  
 Rq=Rectangle  
 Sd=Solder