



**Splice Connector**  
**T&B Catalog Number:**

**UPC Number:**  
**Status:**  
**Description:**

RAA217  
 78621081796  
 Active

Expanded Vinyl Insulated Butt Splice, Length 1.13 Inches, Width .25 Inches, Maximum Insulation Diameter .155, Wire Range #22-#18 AWG, Color Red, Copper, Tin Plated, 1,000 Pack

**WEB\_USE**

US Cutsheet PDF Catalog Link <http://www-public.tnb.com/contractor/docs/stakon.pdf>

**Features**

In butt splices, the wires are butted together and crimped at each end of the splice. These splices are color-coded according to wire size.



**General**

|                 |                          |
|-----------------|--------------------------|
| Insulation Type | Expanded Insulated Vinyl |
| Terminal Series | RAA                      |
| Material        | Copper                   |
| Finish          | Electro -Tin Plated      |
| Color           | Red                      |
| Wire Range      | 22-18                    |

**Dimension Information**

|                             |      |
|-----------------------------|------|
| Maximum Insulation (inches) | .155 |
| Stock Thickness             | .03  |
| A (inches)                  | 1.13 |
| B (inches)                  | .23  |

**Specifications**

|                     |           |
|---------------------|-----------|
| Temperature Rating  | 105°C     |
| Voltage Rating      | 600V      |
| Flammability Rating | UL 94 V-0 |

**Tooling**

|                   |  |
|-------------------|--|
| Tool Charts       | Available on Website                     |
| Application Tools | WT145C, WT2000, WT112M, ERG4001, ERG4003 |
| Recommended Tool  | ERG4001                                  |

**Packaging**

|                    |                   |
|--------------------|-------------------|
| T&B Order Multiple | 1000              |
| T&B Inner Pack     | 1000              |
| Package in Units   | 10000             |
| Package Type       | Bulk              |
| T&B Sold in UOM    | Each              |
| T&B Weight Per UOM | 0.25 lbs. per 100 |

**Application Support**

|                   |                      |
|-------------------|----------------------|
| Overview          | Available on Website |
| Wire Guide Tables | Available on Website |

**Certifications**

|                 |     |
|-----------------|-----|
| RoHS Compliance | Yes |
|-----------------|-----|

## Certifications



File Nbr:  
E9809

### For further technical assistance, please contact us...

Thomas & Betts - USA  
8155 T&B Blvd.  
Memphis, TN 38125  
[www.tnb.com](http://www.tnb.com)

T&B Technical Support  
MS 3B-50  
8155 T&B Blvd.  
Memphis, TN 38125

Hours: 7AM - 6PM CDT  
Monday-Friday  
Phone: (888) 862-3289  
Fax: (901) 252-1321  
Email: [techsupport@tnb.com](mailto:techsupport@tnb.com)