


RoHS Compliant  
Pb - Lead Free

Ltr	Revisions	Date	Appr

**Electrical Specifications:**

Nominal Frequency	25.000	MHz	
Temperature Stability	±50	PPM Max	
Aging per Year	±3		
Operating Temperature Range (Extended)	-40 to +85	°C	
Storage Temperature Range	-55 to +125		
Supply Voltage	3.3 ± 5%	Vdc	
Supply Current	12	mA Max	
Output Voltage	Logic High (Voh)	90%	Vdc Min
	Logic Low (Vol)	10%	Vdc Max
Output Symmetry	40 to 60	%	
Output Load	15	pF HCMOS	
Rise and Fall Time	10	ns Max	
Enable-Disable Function	Tri-State	-	

**Mechanical Specifications:**



11-3 Chien-Kuo Rd T.E.P.Z. 4027 Taiwan, ROC

All dimensions are millimeters.

CAD: TR

Review: SL

Appr: AL

Page: 1/1    Date: Jan. 16, 2008

Specification Title:

**Clock Oscillator**

**7 x 5 mm SMD**

**Product Specification**

**Farnell Order Code: 1538884**

Part Number: **S73305-25.000-15-X**