



EFC200

UPC Number: 78621078966 Status: Active

Description:

2 Inch Black Corrugated PVC I	Flexible Tubing
Features	
	Maximum flexibility in tight applications.
	Extremely fast installation
	Liquidtight with specified fittings.
	Good tensile strength provides excellent pullout protection and smooth inner diameter allows easy wire pulling.
Application	
	Protection of fiber optic cable, installation of instru- mentation and control cable, indoor and outdoor lighting, packaging equipment, marine and ship- board wiring, and flexing-component wiring protec- tion on robots, graphic arts equipments, etc.
General	aon on roboto, grapino arte equipmente, etc.
Material	PVC
Color	Black
Working Temperatures	-18 C to +60 C
Dimension Information	
Size (inches)	2
I.D Minimum (inches)	2.02
I.D Maximum (inches)	2.045
O.D Minimum (inches)	2.34
O.D Maximum (inches)	2.375
Packaging	
T&B Order Multiple	50
Package in Units	50
T&B Sold in UOM	Feet
T&B Weight Per UOM	52 lbs. per 100
Application Support	
Guide to Nonmetallic Conduit Applicat	ionsAvailable on Website
XTRAFLEX System Specifications	Available on Website
Certifications	

Yes



RoHS Compliance

Certifications

File Nbr: E 96548

For further technical assistance, please contact us...



Memphis, TN 38125 www.tnb.com 8155 T&B Blvd. Memphis, TN 38125 Phone: (888) 862-3289 Fax: (901) 252-1321 Email:techsupport@tnb.com