



Einhell

EXPERT

TE-AG 230/2000

Angle Grinder
Art.-No.: 4430840
Ident-No.: 11012

The angle grinder TE-AG 230/2000 is a robust and powerful tool for real experts with exacting demands, which offers outstanding performance on challenging cutting, grinding and roughing jobs everywhere in the home, workshop and garage. Its disk guard with quick-adjust facility can be adapted with just a twist of the hand to any task, while the spindle lock permits easy and speedy tool change. A soft start function ensures that the tool starts up smoothly and safely.

Features

- Solid two-hand operated angle grinder with low-vibration running
- Perfectly suited for high abrasive grinding as well as cutting
- With softstart for safe operation and to limit starting current
- Ergonomic softgrip areas for more comfort and safety
- User-friendly disc guard quick adjustment
- Easy disc change by the use of spindle lock button
- 2nd handle can be fitted in 3 positions flexible due to application
- Durable aluminium metal gear head for tough on-site jobs
- Big radius of action due to 3m long and sturdy rubber cable
- With innovative cable clip to fix wound-up cable
- Delivery including flange nut wrench, without grinding disc



Technical data

- | | |
|-----------------|------------------------|
| • Mains supply | 230 V 50 Hz |
| • Power | 2000 W |
| • Idle speed | 6500 min ⁻¹ |
| • Disc diameter | 230 mm |



Logistic data

- | | |
|----------------------|--------------------|
| • Product weight | 5.9 kg |
| • Gross weight | 6.8 kg |
| • Packing dimensions | 540 x 140 x 160 mm |
| • Bar code | 4006825 593419 |
| • Sales unit | 2 pcs |



www.tuv.com
ID 100000000