

MM20-301B *ULTRA HD*

3 x 1 HDMI source switch HDMI 2.0v HDCP2.2 4K2K 60Hz (fps) 12 bit colour depth



Model	MM20-301B 3 x 1 UHD HDMI source switch
Input	3 HDMI female inputs
Output	1 x HDMI female output
HDCP Protocol	HDCP 2.2
HDMI format	HDMI 2.0
Resolution support (1)	4K2K @30Hz 24bit colour depth
Resolution support (2)	4K2K @60Hz 12bit colour depth 3D frame sequential video format 1080p @ 60Hz
Digital Audio Format	Dolby True HD DTS-HD Master Audio LPCM 7.1CH
Video Bandwidth	300MHz / 10.2Gbps
LED Indicators	Power, In 1, In 2, In 3 input indicators
Manual / IR Control	Manual switch + 38KHz IR remote control and sender included in delivery
Power requirement	5V /1.0A DC Power supply included in delivery
ESD Protection	±8kV (air gap discharge) : ±4kV contact discharge
Dimension / Weight	64mm x 155mm x 17mm / 180g
Operation temperature	-20°C to +60°C