

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** **1200060018**  
**Status:** **Active**  
**Overview:** Brad® Micro-Change® (M12) Connectors  
**Description:** Micro-Change® (M12) Single-Ended Cordset, 4 Poles, Female (Straight) to Pigtail, 0.34mm<sup>2</sup> PUR/PVC Cable, 2.0m (6.56') Length

**Documents:**

[Drawing \(PDF\)](#) [RoHS Certificate of Compliance \(PDF\)](#)

**General**

Product Family	Industrial Cordsets
Series	120006
Connector End A	Micro-Change® (M12)
Connector End B	Pigtail
IP Rating	IP67
Overview	<a href="#">Brad® Micro-Change® (M12) Connectors</a>
Product Name	Micro-Change® (M12)
Protocol	N/A
Region	Europe
Type	Single Ended
UPC	800756927398

**Physical**

Cable Diameter	5.30mm (.209")
Cable Length	2.0m (6.56')
Color - Cable Jacket	Black
Coupling Style	Threaded
Gender	Female-Pigtail
Keyway	Single
LED Indicator	No
Material - Cable Jacket	PUR/PVC
Material - Connector Body	PUR
Material - Contact	Copper Alloy
Material - Coupling Nut	Nickel-plated Brass
Material - O-Ring	Viton
Material - Plating Mating	Gold over Nickel
Orientation	Straight
Poles	4
Temperature Range - Operating	-20°C to +80°C
Wire Size AWG	N/A
Wire/Cable Type	EU Cable

**Electrical**


Current - Maximum per Contact	4.0A
Voltage - Maximum	250V AC/DC

**Material Info**

Old Part Number	804000P03M020
-----------------	---------------

**Reference - Drawing Numbers**

Sales Drawing	SD-120065-105
---------------	---------------



*Series image - Reference only*

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant/Exempted**

**REACH SVHC**

Contained Per -  
ED/79/2015 (17  
December 2015)  
2,4-Di-tert-butyl-6-(5-  
chlorobenzotriazol-2-  
yl)p

Di-(2-  
ethylhexyl)phthalat

**Halogen-Free**

**Status**

**Not Low-Halogen**

**Need more information on product environmental compliance?**

Email [productcompliance@molex.com](mailto:productcompliance@molex.com)  
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS  
ELV

50 Image  
Not Relevant

**Search Parts in this Series**

[120006](#) Series