

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number: [1210120076](#)
Status: **Active**
Overview: mPm® DIN Valve Connectors
Description: mPm® DIN Base, Form A, B26 Base, 3 Pole Plus Ground Terminal, 250V AC/300V DC, Black Nitrile Gasket with Screw

Documents:

Drawing (PDF)	Test Summary STR-1467 (PDF)
Packaging Specification PK-121012-B26 (PDF)	RoHS Certificate of Compliance (PDF)

General

Product Family	Field Attachable / Accessories
Series	121012
Form	A
IP Rating	IP65, IP67
Overview	mPm® DIN Valve Connectors
Product Name	mPm®
Type	Field Attachable Connector
UPC	883906318185

Physical

Cable Diameter	N/A
Coupling Type	N/A
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	N/A
Keyway	None
Material - Connector Body	Polypropylene
Material - Contact	Brass
Material - Coupling Nut	N/A
Material - Plating Mating	Silver
Net Weight	11.730/g
Orientation	Straight
Pitch - Mating Interface	18.00mm
Poles	3
Temperature Range - Operating	-40°C to +90°C
Wire Size AWG	N/A

Electrical

Current - Maximum per Contact	16.0A
Voltage - Maximum	250V AC / 300V DC

Material Info

Old Part Number	B263000N2
-----------------	-----------

Reference - Drawing Numbers

Packaging Specification	PK-121012-B26
Sales Drawing	SD-121012-002
Test Summary	STR-1467

EU ELV

Not Relevant

EU RoHS

Not Compliant

REACH SVHC

Not Contained Per
-ED/79/2015 (17
December 2015)

Halogen-Free

Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com
Please visit the [Contact Us](#) section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

Search Parts in this Series

[121012 Series](#)