



# Introducing 3M™ Terminal Kits

## Performance you can rely on. Trial size kits to prove it.

3M™ Terminal Kits are a great way to experience firsthand what has kept 3M a leading supplier of terminals for more than 30 years. It's not just performance that has electricians and contractors coming back, it's also the speed of installation. It's about:

- Easy wire insertion and insulation entry
- No strand hang-ups
- Withstanding temperature and weather demands

See for yourself. These new kits give you a sampling of best-in-class terminals in convenient packaging that's portable and refillable.



### **3M™ Scotchlok™ Heat Shrink Terminal Kit (SHSTK-1):**

#### **120 assorted pieces**

A selection of our premier line of terminals, connectors and disconnects offering moisture protection, corrosion resistance and durability.

### **3M™ Highland™ Terminal Kit (HTK-1):**

#### **180 assorted pieces**

A selection of our most popular vinyl insulated ring, fork, butt splice and disconnect terminals. UL LISTED and CSA Certified.

# Portable kits are compact, durable and refillable – high performance has never been so easy.

Trial Size Kits			3M™ Scotchlok™ Heat Shrink Terminal Kit	3M™ Highland™ Terminal Kit
<i>A selection of the most popular terminals in 2 handy kits.</i>		<b>3M Part Number:</b> <b>UPC Number:</b> <b>Case Qty (MOQ):</b>	<b>SHSTK-1</b> 00-51128-61360-3 4 kits	<b>HTK-1</b> 00-51128-61359-7 4 kits
Kit Contents	Conductor Size	Stud Size	10 each, 120 pieces total	15 each, 180 pieces total
Ring	22-18 AWG	8	MH18-8R/L	RV18-8
		10	MH18-10R/L	RV18-10
	16-14 AWG	8	MH14-8R/L	RV14-8
		10	MH14-10R/L	RV14-10
	12-10 AWG	8	MH10-8R	RV10-8
		10	MH10-10R	RV10-10
Butt Connector	22-18 AWG	N/A	MH18BC	BSV18
	16-14 AWG	N/A	MH14BC	BSV14
	12-10 AWG	N/A	MH10BC	BSV10
Fork	22-18 AWG	10	MH18-10FL	BFV18-10
	16-14 AWG	10	MH14-10FL	BFV14-10
Female Disconnect	16-14 AWG	Connects to 0.25" male tab	MNHU14-250DFI	FDV14-250

Note: For your convenience, each kit is designed with a compartment for a crimp tool, sold separately.



## Electrical Markets Division

6801 River Place Blvd.  
Austin, TX 78726-9000

Phone 1-800 245 3573  
Fax 1-800 245 0329

Web [www.3M.com/terminals](http://www.3M.com/terminals)

**Important Notice :** Before using 3M product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use.

**Warranty; Limited Remedy; Limited Liability:** 3M's product warranty is stated in its Product Literature available upon request. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If 3M product is defective within the warranty period stated, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any direct, indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.

3M, Scotchlok and Highland are trademarks of 3M company.

© 3M 2016. All rights reserved. Issued: August 2016 Lit # 80-6016-0843-5 (Janz)