

# Air Sample Tube – 24”

MPN: SD-T24



Rigid metal sampling tubes are available in several lengths. They can be installed without the need to open the detector. Sampling tubes install from front-side or back-side of housing.

#### Features:

- Compatible with: Four-wire Duct Smoke Detector **SD-4WJ**
- Accessory Type: Air Sample Tube, 24”
- Operating Temperature Min: -29°C
- Operating Temperature Max: 70°C