


LED Panel Series



VT-1207

HIGHLIGHTS :

WATTS



12

EQ. WATTS



48

LUMINOUS



1000

BEAM ANGLE



120

Item No	: VT-1207
SKU Code	: 4868
Watts	: 12
EQ Watts	: 48
Voltage	: 200-240V,50/60Hz
Lumen(lm)	: 1000
Color Temperature	: 6000K
Beam Angle	: 120
Commercial type	: SQUARE
PF	: >0.6
LED Chip Type	: SMD
CRI	: >80
Energy rating label	: A
Certification	: CE,EMC,ROHS
IP Rating Protection Class	: IP20

Body type	: Aluminum+PMMA+PS
Dimmable	: No
Life Time	: >20000 Hours
Operation Temperature	: -25 ~50°C
EAN code	: 3800230629890
Unit size	: 170x170x25mm
Cutting size	: 155x155mm
Packing details	: 40
Unit cbm	: 0.00162

PRODUCT FEATURES

- Compare with incandescent, it can save over 80% electric cost
- Contemporary & Elegant Design
- Higher Light Transmission Rate
- No flickering, No U.V Radiation
- No Lead or Mercury content hence Environment friendly
- Suitable for office and general lighting (Conference Room, Showroom, lobby, cabin, kitchen etc.)
- High quality power driver
- Instant light 100% O s
- Temp -20 to + 45°C

CLICK HERE
FOR OTHER RELATED CERTIFICATES

