



## **LED Panel Series**





## VT-1207

## **HIGHLIGHTS:**

WATTS

12

LUMINOUS :Ö:

1000

EQ. WATTS

48

BEAM ANGLE

120

 Item No
 : VT-1207

 SKU Code
 : 4857

 Watts
 : 12

 EQ Watts
 : 48

**Voltage** : 200-240V,50/60Hz

 Lumen(Im)
 : 1000

 Color Temperature
 : 3000K

 Beam Angle
 : 120

 Commercial type
 : ROUND

 PF
 : >0.6

 LED Chip Type
 : SMD

CRI : >80 Energy rating label : A

Certification : CE,EMC,ROHS

IP Rating Protection Class : IP20

Body type : Aluminum+PMMA+PS

Dimmable : N

 Life Time
 : >20000 Hours

 Operation Temperature
 : -25 ~50'C

 EAN code
 : 3800230629784

 Unit size
 : D:170x25mm

 Cutting size
 : D:155mm

Packing details : 40 Unit cbm : 0.0014

## PRODUCT FEATURES

- Compare with incandescent, it can save over 80% electric cost
- Contemporary & Elegant Design
- Higher Light Transmission Rate
- No flickering, No U.V Radiaiton
- No Lead or Mercury content hence Environment friendly
- Suitable for office and genral lighting (Conference Room, Showroom, lobby, cabin, kitchen etc.)
- High quality power driver
- Instant light 100% Os
- Temp -20 to + 45'C

