

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION

Part Number:

1200910001

Status:

Active

Overview:

Brad® Nano-Change® (M8) Products

Description:

Nano-Change® (M8) Attachable Connectors, Straight Female, 3 Poles

Documents:

Drawing (PDF)

RoHS Certificate of Compliance (PDF)

General	
Product Family	Field Attachable / Accessories
Series	120091
IP Rating	IP67
MolexKits	Yes
Overview	Brad® Nano-Change® (M8) Products
Product Name	Nano-Change® (M8)
Type	Field Attachable Connector
UPC	78678832510
Physical	
Cable Diameter	N/A
Coupling Type	Internal Thread
Diagnostics / LEDs	No
Diagnostics Port	No
Gender	Female
Keyway	None
Material - Connector Body	Nylon
Material - Contact	Copper
Material - Coupling Nut	Nickel-plated Brass
Material - Plating Mating	Gold over Nickel
Net Weight	7.651/g
Orientation	Straight
Poles	3
Temperature Range - Operating	0°C to +80°C
Wire Size AWG	N/A
Electrical	
Current - Maximum per Contact	4.0A
Voltage - Maximum	60V AC / 75V DC
Material Info	
Engineering Number	N03FA03124
Reference - Drawing Numbers	
Sales Drawing	SD-120091-002



Series image - Reference only

EU ELV

Not Relevant

EU RoHS

China RoHS

Compliant with Exemption 6(c)

REACH SVHC

Not Contained Per - ED/21/2016 (20 June 2016)

Halogen-Free Status

Low-Halogen

Need more information on product environmental compliance?

Email productcompliance@molex.com

Please visit the Contact Us section for any non-product compliance questions.

China ROHS

50 Image

ELV

Not Relevant

Search Parts in this Series

120091 Series

PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION