

## Typenvergleichsliste / Cross Reference List

### ELU → SIBA

ELU	SIBA	Seite Page	ELU	SIBA	Seite Page
157000	7016974	22	184000	7003209	70
158000	7016975	23	184000	7003409	70
160000	7017373	24	185000	7003509	70
164000	7016072	28	185000	7003709	70
164050	7015972	28	186000	7003810	71
164500	7016371	29	186000	7004010	71
164550	7016271	29	187000	7004110	71
165000	7016002	30	187000	7004310	71
165050	7015902	30	189000	7005960	62
166000	7016073	31	189020	7006563	63
166050	7015973	31	189100	7005961	65
166500	7016376	32	189140	7006565	66
166550	7016276	32	189500	7005976	67
166602	7115801	74	190000	7000181	50
171100	7000401	41	196000	7005437	33
171525	7000234	52	199073	7400102	74
171526	7001004	54	199207	7400103	74
171530	7000334	58	204000	7300101	85
172000	7000102	42	204100	7300102	85
172100	7000402	42	7000140	7000140	36
172200	7000702	43	7000740	7000740	37
172525	7000202	52	7001205	7001205	57
172525	7000502	52	7001407	7001407	57
172526	7001005	55	7001607	7001607	57
172526	7001105	55	7001707	7001707	57
172530	7000302	58	7001908	7001908	53
172530	7000602	58	7008913	7008913	56
172900	7500102	51	7012540	7012540	59
173100	7000403	48	157000GT	7017074	22
179020	7000134	39	158000GT	7017075	23
179021	7000733	40	160000GT	7017473	24
179120	7000135	44	164000GT	7016172	28
179150	7000179	45	164500GT	7016471	29
179200	7000765	46	165000GT	7016102	30
179500	7000176	49	166000GT	7016173	31
179900	7500135	51	166500GT	7016476	32
179901	7500134	51			
183000	7014311	69			

### SIBA → ELU

SIBA	ELU	Seite Page	SIBA	ELU	Seite Page
7000102	172000	42	7005961	189100	65
7000134	179020	39	7005976	189500	67
7000135	179120	44	7006563	189020	63
7000140	7000140	36	7006565	189140	66
7000176	179500	49	7008913	7008913	56
7000179	179150	45	7012540	7012540	59
7000181	190000	50	7014311	183000	69
7000202	172525	52	7015902	165050	30
7000234	171525	52	7015972	164050	28
7000302	172530	58	7015973	166050	31
7000334	171530	58	7016002	165000	30
7000401	171100	41	7016072	164000	28
7000402	172100	42	7016073	166000	31
7000403	173100	48	7016102	165000GT	30
7000502	172525	52	7016172	164000GT	28
7000602	172530	58	7016173	166000GT	31
7000702	172200	43	7016271	164550	29
7000733	179021	40	7016276	166550	32
7000740	7000740	37	7016371	164500	29
7000765	179200	46	7016376	166500	32
7001004	171526	54	7016471	164500GT	29
7001005	172526	55	7016476	166500GT	32
7001105	172526	55	7016974	157000	22
7001205	7001205	57	7016975	158000	23
7001407	7001407	57	7017074	157000GT	22
7001607	7001607	57	7017075	158000GT	23
7001707	7001707	57	7017373	160000	24
7001908	7001908	53	7017473	160000GT	24
7003209	184000	70	7115801	166602	74
7003409	184000	70	7300101	204000	85
7003509	185000	70	7300102	204100	85
7003709	185000	70	7400102	199073	74
7003810	186000	71	7400103	199207	74
7004010	186000	71	7500102	172900	51
7004110	187000	71	7500134	179901	51
7004310	187000	71	7500135	179900	51
7005437	196000	33			
7005960	189000	62			