



Manual Tensioning Tool with Plastic Housing

- EVO7 up to 4.8 mm strap width

Features and Benefits

- Ergonomic, slip-proof handle for a comfortable and secure grip
- Extremely low maintenance
- Fast and precise application with minimum effort (TLC mechanism)
- Convenient and simple tension adjustment
- Extended, slim nose for use in narrow spaces
- Housing made of resilient and lightweight glass fibre-reinforced polyester
- Standard grip span (90 mm) and short grip span (80 mm) available



EVO7.

TYPE	Strap Width max. (G)	Strap Thickness max.	Weight	Article-No.
EVO7	4.8	1.5	0.275 kg	110-70129
EVO7SP	4.8	1.5	0.275 kg	110-70130
BLADEKIT	-	-	-	110-70106

All dimensions in mm. Subject to technical changes.

TLC-Technology: Tension - Lock - Cut

The new EVO7 protects muscles and joints and increases effectiveness

- Less recoil shock reduces impact to the operator's hand
- Application of force is significantly reduced



One Step to the Web!



1: Tension: Tie is tensioned as usual.

2: Lock: When the desired tension is met the locking mechanism locks the tie in place.



3: Cut: Innovative, effortless and less recoil shock cut-off function.