

MODEL No.	SC-1080P-BG-BES
Image Sensor	1/2.7" CMOS Sensor
Resolution	1080P
Signal System	PAL / NTSC
Minimum Illumination	0.001 Lux/F1.2
S/N Ratio	More than 50dB
Synchronous System	Internal
IR Distance	20 Meters (with 14 μ x 18PCS Infrared LED)
IR Power On	Photodiode AUTO Control
Video Output	AHD/CVI/CVBS/TVI
Functions	WDR, DNR, UTC
Power/Current	DC12V(+/-10%)/500mA
Lens	Board Len 3.6mm
Weather Proof	IP66
Dimension (mm)	168(W) x 73.5(H) x 65(D)
Weight (g)	500
Operating Conditions	-10~+50°C RH95% MAX

