



GARDTEC

Part Number:

HP25-24 ("T" Plug)


Wire: **SPT1 2 conductor 105°C, 300 volts**


Lengths: **24" (610mm)**

Other options:

- **terminal connections** (any)
- **heat shrink**
- **labeling**
- **stripping**
- **tinning**
- **three conductor cords**
- **complete wire harness assemblies**
(rated at 105°C, 300 volts)
- **red tracer cords**
(all head configurations and lengths)

Listings:

 **UL listed (E189621, E156798)**
Rated 10 AMP/125 VAC

 **CSA listed (LR76679-1)**
Rated 7 AMP/125 VAC

